

Manufacturer Part #	GS66684
OS	Windows 10 Home
CPU	Core i7-10750H
CPU Speed	2.6 - 5.0GHz
Chipset	HM470
Color	Core Black
Screen Size	15.6" FHD, IPS-Level 144Hz 3ms 72%NTSC, 100%sRGB
Resolution	1920x1080 (16:9)
GPU	NVIDIA® GeForce RTX™ 2060
Video Memory	6G GDDR6
Keyboard	Steel Series per-Key RGB with Anti-Ghost key (84 Key)
Audio	Nahimic 3 / Hi-Res Audio
Speaker	2 x Dynaudio 2W Speakers
Memory	16GB (8G*2) DDR4 2666MHz
HDD Capacity	512GB NVMe SSD
HDD Interface	NVMe
Optical Drive Type	-
LAN	Killer LAN E3100
WLAN	Intel Wi-Fi 6 AX201(2*2 ax)
Bluetooth	BT 5.1
Card Reader	-
Webcam	720p HD Webcam
USB	3x USB 3.2 Gen2
Type-C Port	1x Thunderbolt 3 PD charge ; 1x USB-C USB 3.2
Video Port	HDMI (supports 4K @ 60Hz)
Audio Port	1 Audio Combo
AC Power Adaptor	230W Slim
Battery Pack	4 cell (99.9Whr)
Dimension	14.17"x9.65"x0.71"
Weight	4.63lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)