



SPECIFICATIONS

Panel Size	27" (69cm)
Panel Resolution	1920 x 1080 (FHD)
Refresh Rate	165Hz
Response time	1ms
DYNAMIC REFRESH RATE TECHNOLOGY	G-sync Compatible
ACTIVATED RANGE	30 to 165Hz
Panel Type	IPS
Brightness (nits)	300 nits
Viewing Angle	178° (H) / 178° (V)
Aspect Ratio	16:9
Contrast Ratio	1000:1
DCR	100000000:1
Pixel Pitch (H x V)	0.31125(H) x 0.31125(V)
Surface Treatment	Anti-glare
Display Colors	1.07B (8bits + FRC)
DCI-P3 / sRGB	94% / 132%
Video ports	1x Display Port (1.2a) 1x HDMI (2.0b) 1x Type C (DP alt.)
USB ports	2x USB 2.0 Type A 1x USB 2.0 Type B
Audio ports	1x Earphone out
Active Display Area (mm)	597.6(H) x 336.15(V)
Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Control	5-way OSD navigation joystick
Power Type	External Adaptor 19V 3.42A
Power Input	100~240V, 50~60Hz
Signal Frequency	96.4 to 186.7KHz (H) 30 to 165Hz (V)
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	-75° ~ 75°
Adjustment (Height)	0 ~ 100mm
Adjustment (Pivot)	-90° ~ 90°
Power consumption	25W

FEATURES



eSports Gaming

MSI eSports gaming monitor will enhance your competitive gameplay to ensure you are always at your best levels.



eSports Gaming

MSI eSports gaming monitor will enhance your competitive gameplay to ensure you are always at your best levels.



Compatibility	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.
Carton Dimension (W X H X D)	730 x 490 x 220 mm / 28.74 x 19.29 x 8.66 inch
Dimension (W x H x D)	614.9 x 532.7 x 206.7 mm / 24.21 x 20.97 x 8.14 inch
Weight (NW / GW)	6.05kg / 8.7kg 13.34lbs / 19.18lbs
Frameless Design	Yes
Note	Display Port: 1920 x 1080 (Up to 165Hz) Type C (DP alt.): 1920 x 1080 (Up to 165Hz) HDMI: 1920 x 1080 (Up to 165Hz) The color gamut follows the CIE 1976 testing standard.

CONNECTIONS



1. 5-way joystick navigator
2. 1x Display Port (1.2a)
3. 2x HDMI (2.0b)
4. 1x Type C (DP alt.)
5. 1x Earphone out
6. 1x USB 2.0 Type B
7. 2x USB 2.0 Type A
8. 1x DC jack
9. 1x Kensington lock