

PERFORMANCE

Processor

MediaTek Helio P22T (8C, 4x A53 @2.3GHz + 4x A53 @1.8GHz)

Graphics

Integrated IMG PowerVR GE8320 GPU

Chipset

MediaTek SoC Platform

Memory

4GB Soldered LPDDR4x

Storage

64GB eMCP4x

Expandable Memory

MicroSD card (Up to 128GB)

Card Reader

MicroSD Card Slot

Storage Support

64GB eMCP4x on systemboard

Camera

Front 5.0MP / Rear 8.0MP

Microphone

2x, Array

Speakers

Stereo speakers, Dolby® Audio™

Sensors

- Hall sensor
- Accelerometer (G) sensor
- Gyroscope sensor
- Proximity sensor
- eCompass
- Ambient light sensor (ALS)

Vibrator

Vibrator

Battery

Integrated 7500mAh

Max Battery Life

Standby Time: Over 2 wks
Online Video Playback Time: 12 hr
Talk Time: 30 hrs
Browsing Time: 15 hr
Music playtime: 22 hr

Charging Time

Over 5.5 hr

Power Adapter

5V / 2.0A

DESIGN

Display

10.3" FHD (1920x1200) TDDI 400nits

Touchscreen

10-point Multi-touch

Case Material

Plastic, Metal

Pen

None

Water Proofing

IP52

Dimensions (WxDxH)

244.8 x 153.9 x 8.15 mm (9.63 x 6.05 x 0.32 inches)

Weight

460 g (1.01 lbs)

Case Color

Abyss Blue

SOFTWARE

Operating System

Android 11 (R)

Preinstalled Software

Google

CONNECTIVITY

WLAN + Bluetooth™

11a/b/g/n/ac, 1x1 + BT5.0

WWAN

None

SIM Card

No SIM card

VoiceCall

No

Standard Ports

- 1x headphone / microphone combo jack (3.5mm)
- 1x USB-C 2.0 (support data transfer, OTG and Power Delivery)

Optional Ports (configured)

1x microSD card slot (WLAN model)

SERVICE

Base Warranty

1-year, Depot with 1-year Battery

ACCESSORIES

Bundled Accessories

None

CERTIFICATIONS

Green Certifications

- RoHS compliant
- ENERGY STAR® 8.0

Other Certifications

TUV Low Blue Light certified (Hardware Solution)

MODEL

TopSeller : No

Announce Date : 2021-03-30

EAN / UPC / JAN : 195713637084



Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference