Xerox[®] C310 Color Printer and Xerox[®] C315 Color Multifunction Printer

Work doesn't slow down, and your printer shouldn't either.



XEROX C310, C315



Meet the Xerox C310 Color Printer and Xerox C315 Color Multifunction Printer

Is reliability, security and easy connectivity too much to expect from a printer? Not for small and medium-sized businesses (SMBs) and remote employees who need technology that can keep pace without missing a beat. They need hardworking printers that support productivity rather than stand in the way of it.

Meet the Xerox C310 Color
Printer and the do-it-all Xerox
C315 Color Multifunction
Printer. Ready to work hard
right out of the box, they
have everything small work
teams and home offices need
to stay nimble — quality,
simplicity, dependability
and built-in security at just
the right price.



SETUP IS A SNAP

Get up to speed and back to work without IT assistance thanks to Xerox® Smart Start Software, which automates the installation process. Connect to your home or company Wi-Fi in minutes instead of hours.

WOW WITH COLOR

Elevate your everyday communications and make prints "pop" with brilliant resolution and vibrant color that commands attention and makes data easier to visualize.

QUIET TO YOUR EARS

Ultra-quiet operation and big performance are packed into a compact frame. Even the MFP is small enough for tight spaces, so you can scan, print, copy and fax* with less noise and fewer interruptions.

THE POWER TO DO MORE

Business basics get a boost with high print speeds and robust reliability made for modern workflows. The C315 Color MFP takes it even further with fax, fast color and B&W scanning, duplex scanning for more applications and better paper handling, including more trays for higher capacities

and usage. And with the ability to print Microsoft Office files directly from a USB drive, the C315 Color MFP makes it even easier to keep work moving.

TRUE MOBILE FLEXIBILITY

Built-in mobile Wi-Fi connectivity, Apple AirPrint, Mopria and Wi-Fi Direct® give you the power to print how you please from all your favorite devices — smartphones, tablets, desktops, laptops or Chromebooks.

ONE-TOUCH CONVENIENCE

Simplicity drives productivity with Xerox® Print Drivers and the Xerox® Print and Scan Experience App. Get more out of every click with quick access to printer presets and print functionality from your laptop or desktop. Auto-straightening, auto-cropping images and receipt scanning features make scanning on the C315 Color MFP a breeze.

COMPREHENSIVE SECURITY

End-to-end security features protect against rising and increasingly sophisticated cyber threats, keeping sensitive data and documents safe.

Make the move to multifunction with the Xerox C315 Color Multifunction Printer.

When you need to digitize documents to share them with colleagues, make copies or send a fax on the fly, the C315 does it all. The all-in-one device delivers functionality beyond print — without the extra expense or desk space of additional devices.

DO MORE WITH XEROX® WORKFLOW CENTRAL PLATFORM


Small and mighty, there's little the Xerox C315 Color MFP can't do. Print, scan, copy and fax — of course.

But how about being able to:

- Convert your documents into other languages
- Change handwritten notes into shareable, editable documents
- · Create audio files of your reports to listen to in the car
- Automatically redact content for confidentiality
- Convert scans into Microsoft Office formats
- Summarize long documents for guicker reading

Plus, access advanced capabilities such as combination workflows and seamless file routing to cloud repositories.

Ready to find out what your new assistant can do? Learn more and see how to try it for yourself at xerox.com/WorkflowCentral.



KEY HIGHLIGHTS



Xerox C310 Color Printer


- 35/33 ppm Letter/A4 color and B&W
- Two-sided printing
- · Compact footprint
- Built-in Wi-Fi connectivity with Wi-Fi Direct®
- · AirPrint, Mopria and Chromebook printing



Xerox C315 Color Multifunction Printer

Same as C310 Printer plus:

- Copy, scan and fax capabilities
- · Reversing Automatic Document Feeder and platen – up to 50 ipm
- · Scan to email, USB, desktop
- Simple user experience
- New capabilities with optional Xerox Workflow Central



6 Front-side USB port

Manual feed slot

4 125 sheet output tray

7 50-sheet Automatic Document Feeder

5 4.3-inch color touch screen

ECO EXCELLENCE

Blue Angel and EPEAT — the highest internationally recognized standards for environmental performance — translate to less waste, more uptime and lower running costs with long-lasting, high capacity toner. Reducing your eco-footprint is easy with our Green World Alliance* program, which offers hassle-free toner cartridge recycling.



^{*} Not all countries support Green World Alliance. Please check local legislation.

Xerox C310 Color Printer and C315 Color Multifunction Printer

DEVICE SPECIFI	CATIONS	XEROX C310	XEROX C315					
Speed ¹		Up to 35 color/B&W ppm Letter/Up to 33 color/B&W ppm A4	·					
Duty Cycle ²		Up to 80,000 pages/month						
Processor		1 GHz Dual Core	1.2 GHz Quad Core					
Memory		1GB RAM	2GB RAM					
Connectivity		Hi-Speed USB 2.0, Gigabit Ethernet, Hi-Speed USB (Type B), V	Vireless 802.11 b/g/n					
Weights and Dime	ensions (H x W x D)	12.1 x 17.4 x 16.6 in/46 lb	18.2 x 17.4 x 23.1 in/60 lb					
3		308 x 442 x 421 mm/21 kg	462 x 442 x 588 mm/27.1 kg					
Copy and Print Res	solution	Print Only: 1200 x 1200 dpi, 4800 Color Quality	Copy: 600 x 600 dpi					
			Print: 1200 x 1200 dpi, 4800 Color Quality					
First-copy-out Time	e	N/A	As fast as 9.1 seconds color/8.2 seconds B&W					
First-print-out Time	e	As fast as 7.2 seconds color/6.7 seconds B&W	As fast as 8.0 seconds color/7.9 seconds B&W					
Page Description Languages		PCL® 5/6, PostScript® 3, XPS						
Print Features ³		One Touch UI, Print Quality, Normal, Secure, Saved and Sample Set Job Types, Duplex, Orientation, Collation, Print Job ID in Margins,						
		Draft Mode, N-up, Booklet Layout, Watermark, Tray and Toner Status, Rotate Image 180 Degrees, Saved Settings, Earth Smart Settings						
Mobile Printing		Apple AirPrint, Mopria Print Service, Chromebook, Wi-Fi Direct®						
Scan		N/A	Flatbed Scanner with RADF. B&W and color scanning up to					
			600 x 600 dpi. Scan Speed: B&W: Up to 50/47 ipm Letter/A4					
			simplex, 23/21 ipm duplex; Color: Up to 32/30 ipm Letter/A4 simplex,					
			14/13 ipm duplex. Scan Destinations: Email, front-side USB drive, FTP,					
			Network or USB connected computer, Windows Network folder. Scan					
			Formats: TIFF, JPEG, non-searchable PDF, JPEG, BMP, XPS					
Fax	,	N/A	Max 33.6K bps, V.34 Half-Duplex Kbps. MH/MR/MMR/JBIG/JBIG2/JPEG					
			Compression Auto Answer, Auto Redial, Auto Reduction, Broadcast					
			Send, Junk Fax Filter, Fax Address Book, Fax Forward includes:					
			Fax, Email, FTP, Network Folder, Called Number					
Security		Digitally Signed Firmware Updates, Certificate Management, Secure Password Reset, TCP Connection Filtering, Port Filtering, Access Controls,						
		Confidential Print, Non-Volatile Memory Wipe, Fax/Network Separation, Protected USB Ports, Auto-insertion of Sender's Email Address, Login Restrictions						
Print Drivers		Windows® 8, 8.1 Update 1, 10, 11. Windows Server® 2008 SP2 (32- and 64-bit), Windows Server 2008 R2 SP1, Windows Server 2012,						
Tille Dilvers		Windows Server 2012 R2, Windows Server 2019, macOS 10.14, 10.15, 11, 12. For more information about supported Operating Systems, please visit our Drivers & Downloads page and specify your device at www.support.xerox.com						
					Optional Cloud Ser	rvices	N/A	Do more with Xerox Workflow Central
					MEDIA HANDLI	ING		
Main Tray		Up to 250 sheets of 20 lb bond/75 gsm; A4/Letter, A5, A6 and	d custom sizes: 3.8 x 5.8 in to 8.5 x 14 in/98 x 148 mm to 216 x 356 mm					
Manual Feed Slot		1 sheet of 20 lb bond/75 gsm; A4/Letter, A5, A6 and custom s	sizes: 3 x 5 in to 8.5 x 14 in/76 x 127 mm to 216 x 356 mm					
550 plus 100 Shee	t 100 Sheet Tray	Up to 100 sheets of 20 lb bond/75 gsm; A4/Letter, A5, A6 and	d custom sizes: 3 x 5 in to 8.5 x 14 in/76 x 127 mm to 216 x 356 mm					
Tray (optional)	550 Sheet Tray	Up to 550 sheets of 20 lb bond/75 gsm; A4/Letter, A5 and cu	stom sizes: 5.83 x 8.27 in to 8.5 x 14 in/148 x 210 mm to 216 x 356 mm					
Paper Output		Up to 125 sheets of 20 lb bond/75 gsm paper, face down	Up to 150 sheets of 20 lb bond/75 gsm, face down					
Media Types			per and Vinyl Labels), Envelope, Colored Paper, Letterhead, Preprinted, Bond,					
51		Glossy, Rough/Cotton, Recycled						
Reversing Automa	tic Document Feeder	N/A	Up to 50 sheets of 20 lb bond/75 gsm; sizes from A6 SEF					
.			(4.1 x 5.8 in/105 x 148 mm) to Legal (8.5 x 14 in/216 x 355 mm)					
Media Weights	Reversing Automatic	N/A	14 to 32 lb bond/52 to 120 gsm					
. J	Document Feeder							
	Main Tray	16 to 53 lb/60 to 200 gsm	·					
	Manual Feed Slot	16 to 53 lb/60 to 200 gsm						
	550 plus 100 Sheet Tray							
Device Manageme		Xerox® Embedded Web Server, Xerox® CentreWare® Web, Em	gil Alerts. Apple Boniour®					
= =::ce imanagem		Jaca free Serrei, neron Generala Mes, Em	and the transfer of the transf					

¹ Declared print speed in accordance with ISO/IEC 24734, ² Maximum volume capacity expected in any one month. Not expected to be sustained on a regular basis. ³ Some functionality may require software update from xerox.com available Q4 2021 (C310 only).

WHAT COMES IN THE BOX

- Xerox C310/C315 Product
- $\bullet \quad \text{Pre-installed Starter Capacity CMY Print Cartridges: 1,000 print capacity}^4; K \ \text{cartridge: 1,500 print capacity}^4; Cartridge: 1,500 print capacity}^4; K \ \text{cartridge: 1,500 print capac$
- Software and Documentation CD (with User Manual, Quick Install Guide, Safety, Regulatory, Recycling and Print Drivers, and Warranty Statement)
- Installation Guide Product Safety Sheet
- Quick Use Guide
- Power Cord

CERTIFICATIONS

To view the latest list of certifications, go to ${\bf xerox.com/OfficeCertifications}$.

SUPPLIES AND OPTIONS

Standard-Capacity Toner Cartridges:	High-Capacity Toner Cartridges:		
Genuine Xerox Black: 3,000 pages ⁴	006R04360	Genuine Xerox Black: 8,000 pages ⁴	006R04368
Genuine Xerox Cyan: 2,000 pages ⁴	006R04361	Genuine Xerox Cyan: 5,500 pages ⁴	006R04369
Genuine Xerox Magenta: 2,000 pages ⁴	006R04362	Genuine Xerox Magenta: 5,500 pages ⁴	006R04370
Genuine Xerox Yellow: 2,000 pages ⁴	006R04363	Genuine Xerox Yellow: 5,500 pages ⁴	006R04371
Imaging Kit Black Only: 125,000 pages ⁵	013R00689	Imaging Kit Black and Color: 125,000 pages ⁵	013R00692
Waste Toner Bottle: 25.000 pages	008R13325	550 Sheet Tray plus 100 Sheet Multipurpose Feeder	497N07995

[&]quot;Average standard pages. Declared yield in accordance with ISO/IEC 19798. Yield will vary based on image, area coverage and print mode. Approximate pages. Declared yield will vary depending on job run length and media size/orientation and print mode. For more information, visit office.xerox.com/latest/SUPGL-01.PDF.

WARRANTY STATEMENT

1-year warranty (Geography Dependent)

C315 will become available early 2022.

Discover more at **xerox.com**.

