

7-Port Multi-Format Presentation Switch, 4K 60 Hz HDMI, 4K DP, VGA, YPbPr, AV and USB to HDMI

MODEL NUMBER: **B310-701-4K**



Switches between 7 analog and digital audio/video sources, including 4K HDMI and 4K DisplayPort, and transmits them to one HDMI display.

Features

7-Port Multi-Format Presentation Switch Connects 7 Video Sources to One HDMI Display

This presentation switch connects seven separate digital and analog source devices to your television, projector or monitor's HDMI input and switches between them. The B310-701-4K features HDMI, DisplayPort, VGA + Audio, Component (YPbPr) and Composite (Y) inputs for connecting Windows laptops, cable boxes, media servers, DVD and Blu-ray players, video game consoles and other video sources. Switch from one source to another using the manual push buttons or the included remote control.

Suitable for a Wide Range of Audio/Video Applications for Work or Play

This switch is recommended anywhere a variety of video signals is transmitted to a high-definition display. It is suitable for home theaters, video and multimedia presentations, security applications or digital signage in classrooms, bars, restaurants, conference rooms, lecture halls, exhibition centers and trade shows.

Transmits Video from an Upscaled 1080p All the Way to True 4K

Video resolutions include true 4K (4096 x 2160) at 60 Hz (HDMI), 4K (3840 x 2160) at 60 Hz (DisplayPort), 1280 x 768 at 60 Hz (VGA), 1920 x 1080 at 60 Hz (Component YPbPr) and 1280 x 720 at 60 Hz (Composite Y). This switch automatically upscales lower-resolution content to fit the screen. Use the menu options to change picture mode, aspect ratio, resolution output of each port, color temperature and sound output.

Supports HDCP 2.2 and 4:4:4 Color for Up-to-Date Presentations

HDCP 2.2 compliance allows you to stream 4K Amazon and Netflix content with no complications. This switch also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor. You can also connect a U-disk for audio (MP3), video (MP4, WMA), picture (JPG, BMP) or text (English) via the front-panel USB 2.0 port.

Built-In Audio Extractor Lets You Control Sound

TOSLINK, coaxial and RCA right/left audio ports allow you to connect an amplifier, receiver, soundbar or speakers for optical, digital or analog sound. All three audio ports can be used simultaneously. The B310-701-4K supports uncompressed LPCM digital audio, compressed DTS Digital and Dolby Digital (including DTS-HD and Dolby True HD) digital audio and analog audio.

Plug-and-Play Operation for Quick Setup and Immediate Use

The switch works right out of the box with no software required. Mounting hardware is included for installing the switch on a wall, pole or 19-inch rack. Connect your devices to the switch's ports with user-supplied cables (sold separately), and plug the switch's external power supply into an AC power source.

Highlights

- DisplayPort and HDMI ports support UHD resolutions up to 4K @ 60 Hz (4:4:4)
- Push buttons or IR remote allows seamless switching between multiple video sources
- Digital (TOSLINK, coaxial) and analog (R/L) audio outputs work simultaneously
- Upscaler function improves the quality of analog video transmitted to hi-def display

Applications

- Switch between your laptop, media server, cable box, Blu-ray player, video game console, Roku or other audio/video sources in your home theater
- Connect multiple desktop computers and laptops to one monitor to save desk space
- Create multiple digital signage messages to appear at various times on a 4K HDMI display

System Requirements

- Source devices with HDMI, DisplayPort, VGA, Component, Composite or USB output
- Display device with HDMI input

Package Includes

- B310-701-4K 7-Port Multi-Format Presentation Switch
- IR remote control
- IR receiver head cable
- External power supply with 5 ft. cord (Input: 100–240V, 50/60



Hz, 0.4A; Output: 5V 2A)

- (4) International plug adapters
(North America, U.K., Europe,
Australia)
- Mounting hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332256300
Technology	Component; Composite; DisplayPort; HDMI; IR; VGA/SVGA
VIDEO	
Max Supported Video Resolution	HDMI: 4096 X 2160 @60Hz; DP: 3840 x 2160 @60Hz; YPbPr: 1920 x 1080 @60Hz; VGA: 1280 x 768 @60Hz; AV In: 1280 x 720 @60Hz
Max Supported Color Depth	36-bit Deep Color
HDR Support	No
Chroma Sub Sampling	4:4:4
AUDIO	
Audio Specification	Uncompressed - LPCM and Compressed - DTS Digital, DTS-HD and Dolby True HD for HDMI Input
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240~50/60Hz, 0.4A
External Power Supply Output Specs (V / A)	5V/2A
External Power Supply Cord Length (ft.)	5
External Power Supply Cord Length (m.)	1.5
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 9mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	CE; FCC; GS; TUV; UL; cUL



USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Power (White)
PHYSICAL	
Color	Black
Material of Construction	Iron
Rackmountable	Yes
Unit Dimensions (hwd / in.)	11.81 x 0.81 x 2.95
Unit Packaging Type	Box
Unit Weight (kg)	0.51
Unit Weight (lbs.)	1.12
ENVIRONMENTAL	
Operating Temperature Range	32 to 113°F (0 to 45°C)
Storage Temperature Range	14 to 176°F (-10 to 80°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
COMMUNICATIONS	
EDID Compatible	Yes
IR Remote Extension Support	Yes
CONNECTIONS	
Ports	7
Side A - Connector 1	DISPLAYPORT (FEMALE)
Side A - Connector 2	(3) HDMI (FEMALE)
Side A - Connector 3	3.5MM (FEMALE); HD15 (FEMALE)
Side A - Connector 4	COMPONENT (3xRCA) (RGB); COMPOSITE (RCA) (Y)
Side B - Connector 1	TOSLINK (FEMALE)
Side B - Connector 2	STEREO RCA (2xRCA) (RW)
Side B - Connector 3	RCA (FEMALE)
Side B - Connector 4	HDMI (FEMALE)
FEATURES & SPECIFICATIONS	
Port Selection	Pushbutton; Remote Selector
Displayport Specification	1.2



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

HDCP Specification	1.4; 2.2
Driver Required	No
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>