



ASUS Chromebook Flip C434

The Best Just Got Better!



The stunning new ASUS Chromebook Flip C434 takes convertible Chromebook design to the next level. Its stylish contemporary looks, compact portability and powerful specifications are all designed to let you get things done with no fuss, all day and every day. ASUS Chromebook Flip C434 features a new four-sided NanoEdge 14-inch display — with ultraslim bezels and an incredible 87% screen-to-body ratio — for a truly immersive viewing experience, and the unique 360° ErgoLift hinge lets you work in supreme comfort. There's a world of apps to explore on the Google Play Store¹. When only the best is good enough, ASUS Chromebook Flip C434 delivers.

Crafted to perfection

ASUS Chromebook Flip C434 is styled for today, with a precision-crafted all-aluminum chassis finished with elegant diamond-cut anodized edges. Its refined looks are the perfect match for those who appreciate on-the-go versatility combined with peerless design.

The 13" laptop with a 14" display

ASUS Chromebook Flip C434 is not only slim and light, but the new NanoEdge design gives it an ultracompact footprint, so you can enjoy all the benefits of a 14-inch FHD display in a chassis that's as small as many 13-inch laptops.

Unbounded vision with the NanoEdge display

Designed to give you the most screen area in the least physical space, the new four-sided NanoEdge display is simply breathtaking: it makes any visuals more immersive, with less distraction for your eyes. The ultraslim bezels are just 5mm thin² at the sides for a near-borderless experience, and the crisp, clear, high-resolution screen gives you a beautiful creative workplace.

Breeze through your tasks all day long

Featuring powerful latest Intel® processors, ASUS Chromebook Flip C434 lets you breeze through all your everyday tasks on the go. The power-efficient ASUS Chromebook Flip C434 is designed to last for up to 10 hours³ on a single charge, so you can work or play throughout the day while you're on the move.

No-compromise productivity

The best ultraportable laptop deserves an exceptional keyboard. ASUS Chromebook Flip C434 has a full-size backlit keyboard with an impressive 1.4mm key travel, making typing more comfortable and more accurate. Its large touchpad is cleverly engineered for maximum comfort, accuracy and smooth control, incorporating palm-rejection technology and multitouch gesture support.

Faster, more stable Wi-Fi connections

ASUS Chromebook Flip C434 includes Wi-Fi 5 (802.11ac) for strong, stable signals and fast data-transmission speeds. As an added advantage, Wi-Fi 5 (802.11ac) is less prone to interference from other wireless devices operating on the same frequency band.



Application Explore with Google Play

As well as featuring the best of Google out of the box, ASUS Chromebook gives you full access to the Google Play Store, so you can use all your favorite Android apps for work, play, or creativity.



Security Built-in security features

With its automatic updates and built-in anti-virus protection, ASUS Chromebook Flip C434 frees you from the worry of keeping your device safe, secure and always up to date.



Management Stay fast & Seamlessly

Thanks to the seamless cloud integration, you can easily access everything from any device. ASUS Chromebook opens up a whole new world of freedom!

SPECIFICATIONS | C434

| Model | ASUS Chromebook Flip C434 |
|-----------------------------|---|
| Processor | Intel® Core™ M3-8100Y Intel® Core™ i5-8200Y Intel® Core™ i7-8500Y |
| Operating System | Chrome OS |
| On Board Memory | LPDDR3 4GB / 8GB (1867MHz) |
| Memory Slot | N/A |
| Memory Max. | up to LPDDR3 8GB (1867MHz) |
| Storage | eMMC 32GB / 64GB / 128GB |
| Display | 14" FHD (1920x1080), 300nits, sRGB 100% (NTSC: 72%), LED backlit, Wide view, Touch |
| Touch Panel | Yes |
| External Video display Mode | N/A |
| Discrete GPU | N/A |
| Integrate GPU | Intel® HD Graphics 615 |
| Video Camera | HD Web Camera |
| Fingerprint | N/A |
| Wireless | 802.11ac + Bluetooth 4.0 (Dual band) 2x2 |
| LAN | N/A |
| Card Reader | Spec: SD, SDHC, SDXC / Type: Micro SD |
| Interface | 2 x USB 3.1 Gen 1 Type-C™ (up to 5Gbps, power delivery and DisplayPort support) 1 x USB 3.1 Gen 1 Type-A 1 x microSD card reader 1 x Headphone-out & Audio-in Combo Jack |
| Audio | Built-in microphone Built-in Stereo 2W Speakers |
| Weight | 1.45kg |
| Dimension | 32.1 (W) x 20.2 (D) x 1.57 (H) cm |
| AC Adapter | 45W AC Adapter, Plug Type : USB Type-C Output : 15V DC, 3A, 45W Input : 100 -240V AC, 50/60Hz universal |
| Battery | 48Whrs, 3S1P, 3 cell Li-on |
| Keyboard Type | Backlit Keyboard |
| Security | Google H1 security chip |
| Warranty | Vary by specification and region |
| Color | Spangle Silver |

1. Internet connection required. Android and Google Play are trademarks of Google LLC.

2. The stated 5mm width of the side bezel is the distance between the edge of the non-active screen display area and the inside edge of the case. If the case width is included, the side bezel width is 5.3mm. The stated width of the bottom bezel is the distance between the edge of the non-active screen display area and the visible edge of the display when the laptop is opened to 90°. Measured based on standard (not anti-glare) display configuration.

3. Battery performance is based on a mix of standby, web browsing and other use. Charging time requires the battery to be at least 5% charged, the device to be inactive and using the included charger. Actual results may vary.

4. Unless otherwise stated, Wi-Fi speeds are based on theoretical performance. Actual performance may vary.

5. Auto-updates and auto backup require an internet connection.

HINGE

Precision-engineered versatility

Featuring a precision-engineered mechanism, the versatile 360° ErgoLift hinge on ASUS Chromebook Flip C434 has a silky-smooth action that holds the display securely at any angle. This innovative hinge has a dual action that lifts and tilts the keyboard into the perfect typing position when the display is rotated into laptop mode. It also helps enhance the powerful audio, by creating extra space underneath the laptop.



360° ErgoLift hinge



Improved typing position



Enhanced audio performance



Tablet mode



Tent mode




Stand mode

Precision-engineered versatility

Featuring a precision-engineered mechanism, the versatile 360° ErgoLift hinge on ASUS Chromebook Flip C434 has a silky-smooth action that holds the display securely at any angle. This innovative hinge has a dual action that lifts and tilts the keyboard into the perfect typing position when the display is rotated into laptop mode. It also helps enhance the powerful audio, by creating extra space underneath the laptop.

USB-C for ultimate flexibility

Two full-function reversible USB 3.1 Gen 1 Type-C™ (USB-C™) ports make it easy to charge your ASUS Chromebook Flip C434 or connect it to devices and external displays. For maximum convenience and compatibility, there's also a standard USB 3.1 Gen 1 Type-A port, and a microSD slot makes it easy to add extra storage.



3-Year international warranty

100% free of charge,
with no hidden costs.



Pick Up & Return servic

Enjoy a door-to-door service
including pick up, repair, and return.



Warranty extension

Extend service coverage to match
the expected length of use time.