



LIVE STREAMER NEXUS

Audio Mixer / Creator's Control Center

FEATURES



Dual Audio Mix

Independent audio instances with separate volume levels



6 Tracks

3 physical input, 3 virtual tracks




5" Touch Screen

Great color accuracy and screen sensitivity at your fingertips




Widgets

Subs, viewer count, even live chat, all at a glance



LIVE STREAMER NEXUS

CONNECTIONS



Technical Specifications

- **Interface:** USB 2.0, Type B (Driver Required)
- **Mic In:** XLR (Balanced) / 6.3mm (Single-End) x 1
- **Line In:** 3.5mm TRS, Stereo x 1
- **Console In:** Optical In (Toslink) x 1
- **Computer Inputs:** Digital Tracks x 3
- **Headphone Out:** 3.5mm TRS, Stereo
- **Line Out:** 3.5mm TRS, Stereo
- **Output Mix (Independent Instances):**
 - Creator mix
 - Audience mix
- **Sampling Rate:** Up to 96kHz, 24 bits
- **Microphone Effects:** Noise Gate, Reverb, Compressor, Equalizer
- **Frequency Response:** 10Hz to 20kHz
- **Dynamic Range:** 114 dB
- **Screen Panel:** 5" IPS Screen with CTP Touch Panel
- **Widgets:** Interactive & Customizable Grid
- **Rotational Encoders:** 6
- **Lighting:** RGB
- **Function Buttons:** 4
- **Power Switch:** Yes
- **Power Input:** Standard 12V DC, Center Negative, 1.5A
- **Power Consumption:** <7W
- **Dimensions (W x D x H):**
 - Without Stand: 21.7 x 14.5 x 6.1 cm (5.7 x 8.5 x 2.4 in)
 - With Stand: 21.7 x 14.5 x 9.4 cm (5.7 x 8.5 x 3.7 in)
- **Weight:**
 - Without Stand: 0.702 kg (24.76 oz)
 - With Stand: 0.847 kg (29.87 oz)

- Phantom Power +48V, switchable via NEXUS APP

System Requirements

- **Windows:** Windows 10 (64bit)
- **Mac:** macOS 10.15 and above

What's in the box

- Live Streamer NEXUS (AX310)
- Magnetic Kick Stand
- USB 2.0 type B to Type A Cable (1.8 m / 5.9 ft.)
- 3.5 mm TRS Audio Cable (1.8 m / 5.9 ft.)
- 3.5 mm to 6.3 mm Adapter
- Power Adapter
- Quick Guide

Package Dimension:

Unit: 31.1 x 20.9 x 12.4 cm
(12.24 x 8.23 x 4.88 in)

Carton: 44.8 x 33.6 x 45.5 cm
(17.64 x 13.23 x 17.91 in)

Shipping Weight:

Unit: 1.45 Kg (3.2 lbs)
Carton: 10.706 Kg (23.6 lbs)
(6 pcs per carton)

EAN | 4-710710-679958

UPC | 7-9552296660-5