


SL490 Digital Signage



Input and Output Terminals



No.	Name	Description
1	AC Switch	Switch the main power on / off.
2	AC IN	AC power input from the wall outlet.
3	HDMI1 IN / 4 HDMI2 IN	HDMI video / audio input.
5	IR IN / 6 IR OUT	IR signal input / output for the loop-through function.
7	RJ-45	LAN control function for the use of remote control signal from control center.
8	RS232 IN / 9 RS232 OUT	RS232 network input / output for the loop-through function.
10	Audio OUT	Audio output to external AV device.
11	USB PORT B	Touch connector to PC.
12	USB PORT A	USB
13	PC LINE IN	Audio input for VGA source (3.5mm stereo phone).
14	DVI IN	DVI-I video input.
15	DVI OUT	DVI-I video output.
16	DisplayPort IN / 17 DisplayPort OUT	DisplayPort video input / output.
18	MICRO USB	Connect your USB storage device.
19	MICRO SD CARD	Connect your MICRO SD CARD.
20	SECURITY LOCK	Used for security and theft prevention.


Features

- Smart Signage / Closed Android
- Embedded X-Sign Player Supports Playing of Multiple X-Sign Files
- 24/7 Operation
- Landscape / Portrait Display
- Display 4K Daisy Chain
- MDA Software Supports Remote Management
- OTA Function to Continuously Optimize System Performance

Product Specifications

Panel	Screen Diagonal	49"	
	Backlight	LED	
	Resolution	1920 x 1080	
	Aspect Ratio	16 : 9	
	Brightness	450 nits	
	Contrast Ratio	1100 : 1	
	Viewing Angle	178° (H) / 178° (V)	
	Frame Rate	60Hz	
	Response Time	12ms	
	Panel bit	8 bit	
	Light life	50,000 hrs (min.)	
	Orientation	Landscape / Portrait	
	Interface	Input	Power (AC) Inlet × 1
			HDMI × 2
		DVI-I × 1	
		USB × 3 (1 USB 2.0 , 1 for voltage supply, 1 micro USB)	
		RS232 × 1	
		LAN × 1	
Output		Audio out × 1 (3.5 mm Mini Jack Line out)	
		RS232 × 1	
		D-sub × 1	
		HDMI × 1	
	DVI-I × 1		
Speaker	Built-in speaker	10W x 2	
Mechanical	Dimensions (W x H x D)	1097 x 633 x 45.5 mm (without base)	
	Weight (net / gross)	14.7 / 19.9 kg	
Power	Power supply	100V ~ 240V, 50 Hz / 60 Hz	
	Power consumption	67W (typical)	
OSD	On-Screen Display Languages	English / French / Spanish / Simplified Chinese / Traditional Chinese / German / Dutch / Polish / Russian / Czech / Danish / Swedish / Italian / Romanian / Finnish / Norwegian / Greek / Arabic / Japanese / Korean / Thai (21 languages)	
Accessories	Standard	Remote Control × 1	
		Power Cord × 2 (EU, UK)	
		Quick Start Guide × 1	
		VGA (D-sub 15pin) Cable × 1	
		HDMI × 1	
	Optional	Stand × 1	

Dimensions



BenQ Europe B.V.

Meerenakkerweg 1-17
5652 AR Eindhoven
The Netherlands
Tel: +31 88 8889200
Fax: +31 88 8889299

© 2016 BenQ Corp. Specifications may vary by region, please visit your local stores for details. Actual product's features and specifications are subject to change without notice. This material may include corporate names and trademarks of third parties which are the properties of the third parties respectively.

BenQ