



FEATURES

- 31.5-Inch Screen Size / 1920 x 1080 Full HD Resolution
- Long Acting **Antibacterial** Screen
- **SGS** Report Pass the Value of **Antimicrobial** Activity
- Prevent **95%** of **Viruses** and **Bacteria**
- **HDMI / DVI-D / VGA / Audio** Input Connectors
- **10-Point PCAP** Projected Capacitive Touch Technology
- **IP65** Waterproof / **Dust Proof** / **Vandal Proof**
- **Mac™ OS** Compatible
- **3-Year** Warranty

1080P
FULL HD

SPECIFICATIONS

DISPLAY		AB32ZD-OV-45P0
Screen Size		31.5 In
Resolution		1920 x 1080
Backlight		LED
Aspect Ratio		16 : 9
Viewing Angle		178° / 178°
Response Time		8ms
Brightness		300cd/m²
Contrast Ratio		1200 : 1
Color Depth		16.7M
INTERFACE		
HDMI		1
DVI		1
VGA		1
Audio		1
TOUCH TECHNOLOGY		
Type		Projected Capacitive (PCAP)
Points		10-Point
Interface		USB (B-Type)
SPECIAL FEATURES		
Glass		Prevent Bacteria
Waterproof		IP65
Dust Proof		Yes
Vandal Proof		Yes
Support OS		Windows / Linux / Android / Mac
CABINET		
Material		Metal
Color		Black
POWER		
Consumption		50W
Electrical Ratings		AC 100V ~ 240V, 50/60Hz
TEMPERATURE		
Operating		32° F ~ 122° F (0° C ~ 50° C)
Storage		-4° F ~ 140° F (-20° C ~ 60° C)
DIMENSIONS (WxHxD)		
Inch (in)		29.4 x 17.3 x 2.2
Millimeter (mm)		747.4 x 441.3 x 58.6
WEIGHT		
Net Weight		26.4 lbs (12 kg)
COMPLIANT		
Certification		CE
VESA™		
Mount Size (mm)		200 x 200

Specifications subject to change without any notice

AB32ZD-OV-45P0

GVision's most advanced antibacterial monitor can be used in hospitals, restaurants or anywhere else where human hygiene is a concern, the AB Series destroys bacteria and harmful microorganisms on contact. It is chemically bonded to the surface, making it a permanent part of the touch-screen and allowing it to remain functional even after long-term use. SGS Standards Technical Services tested and pass the value of antimicrobial activity against common bacteria.

DIMENSION

Unit: Inch

