

Monitor mount PRO for 2 screens, desk clamp

Article number	508523	Sales unit quantity	1 Piece
Colour	Silver	Sales unit EAN	4005546998404
Packaging unit	1 piece	Packing weight (gross)	3988 G
Base EAN	4005546998404	Country of origin	DE



Logos and awards



Product description

- Monitor mount with desk clamp for 2 screens
- Height, tilt and position of the monitor can be adjusted easily and individually to facilitate ergonomic working
- Can be rotated 360° for working in portrait or landscape mode
- Integrated safety system protects from injury from moving components
- Tidy cable management thanks to five individually attachable cable clips (included)
- Monitors can be moved and fixed freely along the length of the cross beam
- Easy assembly, tools included
- Universal VESA mount (75 x 75 mm or 100 x 100 mm)
- For standard or curved monitors from 21" to 27" [53.34 cm to 68.58 cm] weighing 3 to 8 kg
- Desk clamp for desk thicknesses from 14–44 mm
- 10-year warranty
- Made in Germany
- High-quality materials for a long lifespan: Aluminium and premium plastic
- Environmentally friendly in accordance with ISO 14021

Monitor mount PRO for 2 screens, desk clamp

Product features

Outer width (mm)	780
Outer height (mm)	445
Outer depth / length	190 mm
Filling quantity / Filling quantity for	2 Monitor(s)
Brand	DURABLE
Display Size Monitor	53.3 cm [21"] - 68.6 cm [27"]
Suitable for curved monitors	No
Display rotatable (°)	360
Adjustable display which can be locked in place	Yes
Monitor swivel range	200° horizontal
Monitor Infinitely variable inclination	+ 85° / - 25°
Height adjustment from to	50 - 340 mm
Movement capability	Rotates, tilts, pivots, adjustable height, slidable
Table thickness / pin diameter	14 - 44 mm
Cable Management	Yes
Max. load capacity	Each 3 - 8 kg
VESA standard	75 x 75 mm, 100 x 100 mm
Assembly	Easy to construct
Warranty	10 years
Country of Origin	Made in Germany