


## Key Features

- True 4K HDR visual experience
- 4,000 ANSI Lumens offering bright images in any environment
- Direct Big-screen streaming via USB Type-C
- 4.2ms Ultra-Fast Input & 240Hz high refresh rate
- Warping, auto V keystone and 1.3x zoom for flexible installation



## Product Description

The PX748-4K is a 4,000 ANSI Lumens 4K home projector that shines in value and brightness and delivers pixel-perfect visuals in true 4K clarity with HDR/HLG support. Experience a whole new level of gaming with 4.2ms Ultra-Fast Input, a 240Hz refresh rate, and USB Type-C connectivity for direct streaming from Nintendo® Switch. Set up faster and easier than ever before with powerful warping, auto V keystone, H/V keystone, and 1.3x optical zoom, capable of creating a screen of up to 300" on any surface. Adding on to that is the LAN control capability compatible with home automation systems and 12V trigger output, making the PX748-4K a perfect addition to your smart home.



- 1. Keypad
- 2. Power Key
- 3. Zoom/Focus Ring
- 4. Adjustment Foot
- 5. Lens
- 6. Front IR
- 7. USB Type-C (5V/2A)

- 8. HDMI x 2
- 9. Audio Out
- 10. RS-232
- 11. 12V Out
- 12. USB Type A(5V/1.5A)
- 13. AC In
- 14. RJ45

- 15. Kensington Lock

**Visit Us**  [www.viewsonic.com](http://www.viewsonic.com)

## SPECIFICATION

Native Resolution:	3840x2160
DMD Type:	DC3
Brightness:	4000 (ANSI Lumens)
Contrast Ratio with SuperEco Mode:	12000:1
Display Color:	1.07 Billion Colors
Light Source Type:	Lamp
Light Source Life (hours) with Normal Mode:	4000
Light Source Life (hours) with SuperEco Mode:	20000
Lamp Watt:	240W
Lens:	F=1.94-2.12, f=12-15.6mm
Projection Offset:	120%+/-6%
Throw Ratio:	1.13-1.47
Optical Zoom:	1.3x
Digital Zoom:	0.8x-2.0x
Image Size:	30"-300"
Throw Distance:	0.75m~9.76m(100"@2.50m)
Keystone:	H:+/-40° , V:+/-40°
Lens Shift V. Range:	Up to 20% (Digital)
Lens Shift H. Range:	Up to 20% (Digital)
Audible Noise (Normal):	33dB
Audible Noise (Eco):	28dB
Input Lag:	4.2ms
Resolution Support:	VGA(640 x 480) to 4K(3840 x 2160)
HDTV Compatibility:	480i, 480p, 576i, 576p, 720p, 1080i, 1080p, 2160P
Horizontal Frequency:	15K-135KHz
Vertical Scan Rate:	23-240Hz

## INPUT

HDMI:	2 (HDMI 2.0b, HDCP 1.4/2.2)
USB Type C:	1 (5V/ 2A)

## OUTPUT

Audio-out (3.5mm):	1
Speaker:	10W
USB Type A (Power):	1 (5V/ 1.5A)
12V Trigger (3.5mm):	1

## CONTROL

RS232 (DB 9-pin male):	1
RJ45 (LAN control):	1

## OTHERS

Power Supply Voltage:	100-240V+/- 10%, 50/60Hz(AC in)
Power Consumption:	Normal: 310W Standby: <0.5W
Operating Temperature:	0~40°C
Net Weight:	2.8kg
Dimensions (WxDxH) with Adjustment Foot:	312x222x108mm
OSD Language:	English, French, Spanish, Thai, Korean, German, Italian, Russian, Swedish, Dutch, Polish, Czech, T-Chinese, S-Chinese, Japanese, Turkish, Portuguese, Finnish, Indonesian, India, Arabic, Vietnamese, Greek, Total 23 languages

## STANDARD ACCESSORY

Power Cord:	1
USB-C Cable:	1
Remote Control:	1(w/ backlit)
QSG:	Yes

## OPTIONAL ACCESSORY

Lamp/Light Source:	RLC-127
Carry Bag:	PJ-CASE-008