

Country	ca
Ean	0824142256817
OS	Windows 10 Pro
Color	Titanium Blue
Screen Size / Type	17.3" UHD (3840*2160), 120Hz 100% Adobe
Resolution/ Ratio	3840x2160 16:9
CPU/Processor	Core i9-11980HK
CPU Frequency	2.6 - 5.0GHz
Chipset	HM570
Graphics	NVIDIA® RTX™ A5000
Video Memory	16GB GDDR6
System Memroy	DDR IV 32GB*2
SoDimm	2 Sockets; Max Memory 64GB
HDD Capacity	2TB NVMe PCIe SSD
HDD Interface	NVMe
SSD	1x M.2 SSD Slot PCIe Gen4x4, 1x M.2 SSD Slot PCIe Gen3x4 (Max up to 2TB)
LAN	2.5Gb Lan
WLAN	Killer WiFi 6E AX1675 (2x2 )
TPM	Infineon SLB 9670
BT	BT 5.2
Card Reader	1x SD7.0 (XC/HC)
HDMI-out	4K @ 120Hz / 8K @60Hz
Mini-Display Port	mDP v1.4*1
USB Type C	1 x Thunderbolt 4/ USB4 w/PD charging 1 x USB 3.2Gen 2
USB	1 x USB3.2 Gen 2 2 x USB3.2 Gen 1
Keyboard	White backlight keyboard (102 Key)
Touch Pad	Multi Touch + fingerprint
Mic-in/ Headphone-out	1 combo (Hi-Res Audio)
Speaker	2x 2W Speaker + 2 x 1W Woofers
Webcam	720p HD Webcam
Battery Pack	4 cell (99.9Whr) Li-Polymer
AC Adapter	280W
Unit weight	6.39 lbs
Unit Dimension	15.63"x 10.57"x 1.08"
UPC	824142256817
UCC-14	10824142256814
Warranty	3 year Limited warranty (Include 1 Year Global)