



WS66 11UKT-288CA

OS	Windows 10 Pro (Free upgrade to Windows 11*)
Color	Black
Screen Size / Type	15.6" FHD (1920*1080), Finger Touch panel, 60Hz 72%NTSC
Resolution/ Ratio	1920x1080 16:9
Touch Option	Touch Panel
CPU/Processor	Core i7-11800H 8 Core
CPU Frequency	2.4 - 4.6GHz
Chipset	HM570
Graphics	NVIDIA® RTX™ A3000
Video Memory	6GB GDDR6
System Memroy	DDR IV 16GB*2
SoDimm	2 Sockets; Max Memory 64GB
HDD Capacity	1TB NVMe PCIe SSD
HDD Interface	NVMe
SSD	1x M.2 SSD Slot PCIe Gen4x4, 1x M.2 SSD Slot PCIe Gen3x4 (Max up to 2TB)
LAN	2.5Gb Lan
WLAN	Killer WiFi 6E AX1675 (2x2)
TPM	Infineon SLB 9670
BT	BT 5.2
Card Reader	-
HDMI-out	4K @ 120Hz / 8K @60Hz
USB Type C	1x Thunderbolt 4 1 x USB 3.2Gen2/DP
USB	USB3.2 Gen2 *3
Keyboard	White backlight keyboard (84 Key)
Touch Pad	Silky Glass Touchpad + fingerprint
Mic-in/ Headphone-out	1 combo (Hi-Res Audio)
Speaker	Speakers 2W*2
Webcam	IR 720p HD Webcam
Battery Pack	4 cell (99.9Whr) Li-Polymer
AC Adapter	230W
Unit weight	4.63lbs
Unit Dimension	14.17"x9.65"x0.71"
UPC	824142256961
UCC-14	10824142256968
Warranty	3 year Limited warranty (Include 1 Year Global)