Cyber Power

P606URC2 HOME OFFICE SURGE PROTECTION

Protect home and office computers, electronics, and home theater equipment

The CyberPower Surge Protector P606URC2 prevents spikes in energy caused by storms and electrical power surges from reaching your home electronics such as audio/video equipment, laptops and desk top computers, household appliances and small electronics. The P606URC2 provides 500 joules of surge protection, 6 AC outlets, two USB-A charging ports, and a braided 6-foot power cord with a right-angle plug.

Features of the P606URC2 include automatic shutdown, an EMI/RFI noise filter, metal oxide varistor (MOV) technology, an On/Off switch with integrated 15-Amp circuit breaker, LED indicator, low profile plug, keyhole mounting slots, and damage-resistant construction. This surge suppressor comes with a One-Year Limited Warranty and a \$25,000 Connected Equipment Guarantee.

TYPICAL APPLICATIONS

- Consumer Electronics
- Chargers
- Laptop Computers

FEATURES

- Surge suppression: 500 J
- Outlet type: NEMA 5-15R
- Outlet quantity: 6
- USB-A charge ports: 2
- USB charge output: 2.4A (shared)
- Power cord length: 6 ft
- Power cord type: braided
- Plug style: Right-angle 45° offset
- Volts: 125 V
- Circuit breaker: 15 A
- EMI/RFI Filtration: Yes
- Warranty: One-Year Limited
- Connected Equipment Guarantee: \$25,000

SPECIFICATIONS

INPUT		
Cord Length	6 ft (1.8 m)	
Input Plug Type	NEMA 5-15P	
Maximun Input Current	15A	
Plug Style	Low Profile	
OUTPUT		
Outlets - Total	6	
USB Charge Port - Total	Yes	
USB Charge Port Amperage	5V 2.4A	
USB Charge Port Quantity	2	
USB Charge Port Standard	Туре А	

SURGE PROTECTION & FILTERING		
Clamping Voltage	800 V (H-N)	
EMI/RFI Filtration	150 KHz 100 MHz	
Maximum Surge Current	15,000 amps	
Surge Suppression (Joules)	500 J	
PHYSICAL		
Color	White	
Material of Construction	Plastic	



P606URC2 HOME OFFICE SURGE PROTECTION

SPECIFICATIONS CONT.

PHYSICAL DIMENSIONS		
Physical Dimensions - WxHxD (cm)	4.72 x 3.48 x 30.2 cm	
Physical Dimensions - WxHxD (mm)	47 x 35 x 302 mm	
Physical Dimensions - WxHxD (in.)	1.86 x 1.37 x 11.89 in.	
Weight (kg)	0.32 kg	
Weight (lb)	0.70 lbs.	
SHIPPING DIMENSIONS		
Shipping Dimensions - WxHxD (cm)	4.72 x 6.02 x 30.2 cm	
Shipping Dimensions - WxHxD (mm)	47.24 x 60.2 x 302.01 mm	
Shipping Dimensions - WxHxD (in)	1.86 x 2.37 x 11.89 in.	
Weight (kg)	0.43 kg	
Weight (lb)	0.95 lbs.	

CERTIFICATIONS		
Environmental	RoHS Compliant	
Safety	UL1449 3rd Edition, FCC, cUL	
WARRANTY		
CEG Amount	\$25,000	
Product Warranty	1-Year Limited Warranty	