



## SPECIFICATIONS

<b>Panel Size</b>	24.5" (62.2cm)
<b>Panel Resolution</b>	1920 x 1080 (FHD)
<b>Refresh Rate</b>	360Hz
<b>Response time</b>	1ms GTG
<b>Panel Type</b>	Rapid IPS
<b>Brightness (nits)</b>	400 nits
<b>Viewing Angle</b>	178° (H) / 178° (V)
<b>Aspect Ratio</b>	16:9
<b>Contrast Ratio</b>	1000:1
<b>Active Display Area (mm)</b>	543.168(H) x 302.616(V)
<b>Pixel Pitch (H x V)</b>	0.2829(H) x 0.2802(V)
<b>Surface Treatment</b>	Anti-glare
<b>Display Colors</b>	1.07B (8bits + FRC)
<b>DCI-P3 / sRGB</b>	84.09% / 109.63%
<b>Video ports</b>	1x Display Port (1.4) 2x HDMI (2.0b)
<b>USB ports</b>	3x USB 3.2 Gen 1 Type A 1x USB 3.2 Gen 1 Type B
<b>Audio ports</b>	1x Earphone out
<b>Kensington Lock</b>	Yes
<b>VESA Mounting</b>	100 x 100 mm
<b>Control</b>	5-way OSD navigation joystick
<b>Power Type</b>	External Adaptor 20V 4.5A
<b>Power Input</b>	100~240V, 50~60Hz
<b>DYNAMIC REFRESH RATE TECHNOLOGY</b>	G-SYNC
<b>ACTIVATED RANGE</b>	0 to 360Hz
<b>Power consumption</b>	22W
<b>Signal Frequency</b>	150.9 to 417.16KHz (H) 48 to 360Hz (V)
<b>Adjustment (Tilt)</b>	-5° ~ 20°
<b>Adjustment (Swivel)</b>	-45° ~ 45°
<b>Adjustment (Pivot)</b>	-90° ~ 90°
<b>Adjustment (Height)</b>	0 ~ 130mm
<b>Dimension (W x H x D)</b>	560.1 x 399.3 x 233.7 mm / 22.05 x 15.72 x 9.20 inch
<b>Carton Dimension (W X H X D)</b>	761 x 410 x 207 mm / 29.96 x 16.14 x 8.15 inch

## FEATURES



<b>Weight (NW / GW)</b>	6.47kg / 9.02kg 14.26lbs / 19.89lbs
<b>Frameless Design</b>	Yes
<b>Console Mode</b>	FHD @ 120Hz
<b>Compatibility</b>	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.
<b>Note</b>	Display Port: 1920 x 1080 (Up to 360Hz) HDMI: 1920 x 1080 (Up to 240Hz) The color gamut follows the CIE 1976 testing standard.

## CONNECTIONS



1. 5-way joystick navigator
2. Kensington Lock
3. 2x HDMI (2.0b)
4. 1x Display Port (1.4)
5. 1x Earphone out
6. DC Jack
7. 1x USB 3.2 Gen 1 Type B
8. 3x USB 3.2 Gen 1 Type A