

# #1 TOP RATED SPEAKER SYSTEM

## KLIPSCH PROMEDIA 2.1 THX® CERTIFIED



### LEGENDARY SOUND FROM A LEGENDARY DUO

The Klipsch ProMedia 2.1 THX® Certified Speaker System pairs the legendary sound of Klipsch audio with the revolutionary THX experience. THX engineers conduct more than 2,000 tests on every system to ensure it's of the highest quality and sound performance. Couple that with Klipsch's proprietary technology and you can fill the room with incredible sound for gaming, movies, or music..

### EXCLUSIVE KLIPSCH MICROTRACTRIX® HORN TECHNOLOGY

Klipsch MicroTractrix® horns make a major contribution to the ProMedia's amazing clarity. Their highly efficient design reproduces more sound from every watt of power, controlling the dispersion of that sound and sending it straight to your ears for clarity and lifelike impact no other system can duplicate.

### CLEAN BASS OUTPUT AT ALL VOLUME LEVELS

The two-way satellites' 3" midrange drivers blend perfectly with the ProMedia THX® Certified solid, 6.5" side-firing, ported subwoofer for full bandwidth bass response you can actually feel. Coupled with 200-watts of power, the 6.5" subwoofer creates an immersive sound experience where you'll hear everything, including your opponent when they lose.

### PERFORMANCE FLEXIBILITY

With its plug and play setup and convenient 3.5mm input, the ProMedia THX® Certified 2.1 speaker system offers an easy-to-use control pod. That means a fast change to the volume and subwoofer output. If your neighbors get cranky, simply connect your headphones to game quietly.



# KLIPSCH PROMEDIA 2.1 THX® CERTIFIED

## SPECIFICATIONS

<b>System Power</b>	Total System Power: 100 watts continuous/200 watts peak @ <0.2% THD 260 watts short-term peak power Satellites: 18 watts/channel continuous @ <0.2% THD, 1kHz 26 watts/channel short-term power @ <5% THD, 1kHz Subwoofer: 65 watts continuous @ <0.2% THD, 50 Hz 80 watts short-term power @ <5% THD, 50Hz
<b>Built From</b>	2018
<b>Frequency Response</b>	35Hz ~ 22kHz
<b>Satellite Crossover Frequency</b>	3.5kHz
<b>Enclosure Material</b>	Satellites: ABS Subwoofer: MDF
<b>Enclosure Type</b>	Satellites: Sealed Subwoofer: Bass Reflex
<b>High Frequency Horn</b>	90° x 40° MicroTractrix®
<b>Inputs</b>	3.5mm miniplug
<b>Typical Maximum Output</b>	110dB SPL (in-room)
<b>Outputs</b>	3.5mm miniplug Headphone
<b>Dimensions</b>	Satellite: 8.5" (21.59cm) x 4.2" (10.67cm) x 5.67" (14.4cm) Subwoofer: 9.5" 24.13cm) x 9.8" (24.9cm) x 10.2" (25.9cm)
<b>Finish</b>	Black
<b>Subwoofer</b>	One, side-firing 6.5" (16.51cm) long-throw fiber composite cone
<b>Tweeter</b>	19mm PEI dome
<b>Voltage</b>	110/120 VAC
<b>Weight</b>	Satellite: 2.1lbs (0.95kg) Subwoofer: 17 lbs (7.7kg)
<b>Mfr Part #</b>	1067415

**Klipsch**  
KEEPERS OF THE SOUND

For more information, contact your Ingram Micro representative.  
(800) 456-8000 x76250 | [sourcingteam@ingrammicro.com](mailto:sourcingteam@ingrammicro.com)