



V7 Charging Station - 12 Devices AC US Power

CHGSTA12AC-1N

SKU: 9AZ974

The V7 Charging Station allows you to secure, store and charge up to 12 Chromebook, laptop, or tablet devices with up to 15" screens. It has versatile mounting options including wall mount, table top, or stack two together and add optional casters for mobility. Easy to deploy with numbered shelves, durable device slots and well-designed power management. Numbered device spaces and corresponding individual power supply slots make it easy to use. Made from high-grade 18 gauge cold rolled steel, the Charging Station also features a secure locking door with key, secure power supply compartment, and an option to add your own padlock for extra security to keep devices safe.

- Versatile mounting options - wall mount, place on a table top, or stack two together with optional casters for mobility
- Efficient power distribution for all of your devices from one plug
- Cable management easily organizes power supplies and routes cables to each device
- Secure locking door and power supply compartment keeps devices safe. Option to add your own padlock for extra security
- Easily store and charge almost any Chromebook, laptop, or tablet with screens up to 15"

General

Sku: 9AZ974
 Model: CHGSTA12AC-1N
 EAN: 0662919113020
 Warranty: 2 years
 Compliance: RoHS, UL
 Country Of Origin: China
 Package Type: One Color
 SAP: 5193037
 Package Includes: Charging Station, Power Cord, User manual

Color

Color: Black

Design

Material: High-grade 18 gauge cold rolled steel

Package Dimensions

Package Dimensions (L/W/H): 26.38 x 19.29 x 23.03
 in (670 x 490 x 585 mm)
 Shipping Weight: 77.16 lbs (35 kg)

Product Dimensions

Product Dim (L/W/H): 24.02 x 16.93 x 20.67 in (610 x
 430 x 525 mm)
 Product Weight: 74.96 lbs (34 kg)

Technical

Shelves: Sliding
 Fully Assembled: Yes
 Charging System: Power Distribution Unit (PDU)
 Device Slot Dimensions: 13.74 x 1.38 x 10.7 in (349 x
 35 x 272 mm)
 Storage Temperature : -40°C to +60°C
 Operating Temperature : -10°C to 40°C
 Storage Humidity: 20% to 90% RH
 Operating Humidity : 20% to 80% RH
 AC Cord length: 6 ft (1.83 m)