

Key Features

Pantone Validated Display | Designer Mode | Hardware calibration ready | vDisplayManager | Reduce Clutter
With Single-Cable Solution



Product Description

Engineered to deliver unmatched color accuracy crucial for professional applications, the ViewSonic® VP2756-4K UHD monitor displays your work with the vivid and lifelike color it deserves. With a SuperClear® IPS panel and a sleek 3-sided frameless design, the VP2756-4K provides a near-seamless viewing experience ideal for multi-monitor setups. The VP2756-4K is equipped with USB-C for single cable connectivity to deliver video, audio, and 60W of power delivery. To ensure precise, uniform color, each of our monitors is factory calibrated to deliver an amazing Delta E <2, so you can be confident what you see on screen is what your clients and customers will see as well.



27"
DISPLAY



IPS
PANEL



3840 x 2160
RESOLUTION

Contact Sales

- call: 888.881.8781
- email: salesinfo@viewsonic.com
- visit: viewsonic.com

Display:

Display Size (in.):	27
Viewable Area (in.):	27
Panel Type:	IPS
Resolution:	3840 x 2160
Resolution Type:	4K (3840x2160)
Static Contrast Ratio:	1,000:1
Dynamic Contrast Ratio:	20,000,000:1
Light Source:	LED
Brightness:	350 cd/m2
Colors:	1.07B
Color Space Support:	10 bit (8 bit + A-FRC)
Aspect Ratio:	16:9
Response Time (Typical GTG):	5ms
Viewing Angles:	178° horizontal, 178° vertical
Panel Surface:	Anti-Glare type, Hard-coating (3H), Haze 25%

Compatibility:

PC Resolution (max):	3840 x 2160
Mac® Resolution (max):	3840 x 2160

Connector:

USB Type A(2), USB Type B(1), USB Type C(1), HDMI 2.0 In(1), DisplayPort(1)

Audio:

Internal Speakers:	2W (x2)
--------------------	---------

Power:

Eco Mode (Conserve):	37.5W
Eco Mode (optimized):	39.5W
Consumption (typical):	42W
Consumption (max):	122W
Voltage:	100-240 VAC
Stand-by:	0.3W
Power Supply:	Internal

Additional Hardware:

Kensington Lock Slot:	1
-----------------------	---

Controls:

Physical Controls:	Key 1 (power), Key 2, Key 3, Key 4, Key 5 (favorite)
On Screen Display:	Input Select, Audio Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu

Operating Conditions:

Temperature:	32-104° F (0 - 40° C)
Humidity (non-condensing):	20-90%

Mount:

VESA Compatible:	100 x 100 mm
------------------	--------------

Video Signal:

Frequency Horizontal:	15 ~ 136 KHz
Frequency Vertical:	24 ~ 75 Hz

Ergonomics:

Height Adjust:	130 mm / 5.1 in
Swivel:	60°
Pivot (Right/Left):	90° / 90°
Tilt (Forward/Back):	5° / 21°

Weight (imperial):

Net (lbs):	15.1
Net Without Stand (lbs):	9.8
Gross (lbs):	21.0

Weight (metric):

Net (kg):	6.9
Net Without Stand (kg):	4.4
Gross (kg):	9.5

Dimensions (imperial) (WxHxD):

Packaging (in.):	21.9 x 18.3 x 8.9
Physical (in.):	24.1 x 16.15~21.27 x 8.5
Physical Without Stand (in.):	24.1 x 14.3 x 2.1

Dimensions (metric) (WxHxD):

Packaging (mm):	740.0 x 465.0 x 225.0
Physical (mm):	613.0 x 410.0~540.0 x 215.0
Physical Without Stand (mm):	613.0 x 363.0 x 53.0

General:

Regulations:	cTUVus, FCC-B, ICES003, CEC, MX-CoC, Mexico Energy
PACKAGE CONTENTS:	VP2756-4K, Power Cable, USB-C Cable, HDMI cable, UAB-A/B Cable
Recycle/Disposal:	Please dispose of in accordance with local, state or federal laws.
Warranty:	Three-year limited warranty on parts, labor and backlight
UPC:	766907012972

Accessories:

LCD-DMA-002, MH27M1, VSPF2700
