



DELL 24 MONITOR | SE2422H  
DELL 27 MONITOR | SE2722H



Maximize space and view your screen with fewer distractions with 23.8"/27" Full HD monitors featuring three-sided slim bezels and a compact footprint that frees up valuable desk space.

### Thoughtfully designed

**More screen space:** Slim bezels mean fewer distractions and an improved viewable screen-to-body ratio.

**Sturdy and compact:** Free up your workspace and regain your desk real estate with this small-footprint monitor. A built-in power supply unit and cable holder help to further reduce clutter.

**Adjustable to your liking:** Easily tilt the monitor to get just the right viewing angle or hook it up with a compatible VESA mount.

### Easy on the eyes

**Increase viewing comfort:** Minimize harmful blue light emissions to help reduce eye fatigue with Dell's TÜV-certified ComfortView feature.

**Ease eye fatigue:** Optimize eye comfort and minimize distractions thanks to a flicker-free, anti-glare screen.

**Simplify your screen:** Stay organized and easily manage multiple applications and windows on a single screen using Dell EasyArrange.

### Smooth and lively visuals

For tear-free visuals during leisure gameplay, this monitor comes with AMD FreeSync™ technology, fast response time and features up to 75Hz refresh rate.

### Better for the Environment

**Eco-conscious packaging:** To reduce our manufacturing impact on the environment, this monitor is shipped Styrofoam-free and the packaging is made of at least 75% recycled cardboard.

**Energy conservation:** Save energy when your monitor is not in use with PowerNap<sup>4</sup>, a feature that dims or puts your monitor to sleep when it's not in use.

### A brand you can rely on

As the No.1 monitor company worldwide\* we take pride in our unyielding commitment to quality and the utmost satisfaction of our customers.

Minimize downtime with Dell's Advanced Exchange Service.<sup>2</sup>

FOR MORE INFORMATION, VISIT  
[DELL.COM/MONITORS](http://DELL.COM/MONITORS)



\*Source: IDC Worldwide Quarterly PC Monitor Tracker, Q4 2020

<sup>4</sup>Based on Dell's internal analysis, January 2021—The SE2422H monitor stand base has been reduced by 23% compared to the SE2416H.

# Features & Technical Specifications

## Dell 24 Monitor (SE2422H) / Dell 27 Monitor (SE2722H)

Display	SE2422H	SE2722H
<b>Viewable image size (diagonal)</b>	60.45 cm (23.8")	68.466 cm (27.0")
<b>Active display area (horizontal x vertical)</b>	527.04 mm x 296.46 mm (20.75" x 11.67")	596.74 mm x 335.66 mm (23.49" x 13.22")
<b>Panel technology</b>	Vertical Alignment (VA); anti-glare with 3H hardness	
<b>Maximum resolution</b>	Full HD (1920 x 1080) at 60Hz (VGA) and up to 75Hz (HDMI)	
<b>Aspect ratio</b>	16:9	
<b>Pixel pitch</b>	0.2745 mm x 0.2745 mm	0.3108 mm x 0.3108 mm
<b>Brightness (typical)</b>	250 cd/m <sup>2</sup>	
<b>Color gamut (typical)</b>	72% NTSC (CIE 1931)	84% NTSC (CIE 1976) / 72% NTSC (CIE 1931)
<b>Color depth</b>	16.7 million colors	
<b>Contrast ratio (typical)</b>	3,000 : 1	
<b>Typical viewing angles (vertical / horizontal)</b>	178° / 178°	
<b>Response time (typical)</b>	5ms gray to gray (extreme), 8ms (fast), 12ms (typical)	4ms gray to gray (extreme), 5ms (fast), 8ms (typical)
<b>Backlight</b>	LED edgelight system	
<b>AMD FreeSync™</b>	Yes, supports AMD FreeSync™ technology with refresh rate up to 75Hz	
<b>TÜV-certified</b>	Yes, ComfortView <sup>1</sup> with Flicker-free screen	
<b>Dell Display Manager compatibility</b>	Yes, with Dell EasyArrange	
<b>Connectivity</b>	HDMI 1.4 (HDCP 1.4), VGA	
<b>Stand adjustability</b>	Tilt -5° / 21°	
<b>Stand features</b>	Built-in cable management clip	
<b>VESA mount compatible</b>	Yes, 100 mm x 100 mm	
<b>Security lock slot</b>	Yes (cable lock sold separately)	
<b>Power</b>	100 VAC to 240 VAC / 50 Hz or 60 Hz ± 3 Hz / 1.6 A (max)	
<b>AC input voltage/frequency/current</b>		
<b>Power consumption (Operational)</b>	0.3 W (Off Mode) 0.3 W (Standby Mode) 15.7 W (On Mode) 24.0 W (Max)	0.3 W (Off Mode) 0.3 W (Standby Mode) 20.0 W (On Mode) 24.0 W (Max)
<b>Dimensions (HxWxD)</b>		
<b>Panel only</b>	331.61 mm x 552.64 mm x 49.69 mm (13.06" x 21.76" x 1.96")	369.61 mm x 623.30 mm x 55.56 mm (14.55" x 24.54" x 2.19")
<b>Full monitor (with stand)</b>	420.25 mm x 552.64 mm x 178.81 mm (16.55" x 21.76" x 7.04")	459.21 mm x 623.30 mm x 199.87 mm (17.95" x 24.54" x 7.87")
<b>Weight</b>		
<b>Panel only (for VESA)</b>	3.18 kg (7.01 lbs)	3.80 kg (8.38 lbs)
<b>Monitor and cables with full packaging</b>	5.23 kg (11.53 lbs)	6.37 kg (14.04 lbs)
<b>Environmental compliance</b>	RoHS-compliant, BFR/PVC-reduced monitor (excluding external cables), Arsenic-free glass and Mercury-free for the panel only.	
<b>Standard service plan</b>	(WW) 3-year Advanced Exchange Service <sup>2</sup> & Limited Hardware Warranty <sup>3</sup> (US/Canada) 1-year Advanced Exchange Service <sup>2</sup> & Limited Hardware Warranty <sup>3</sup>	
<b>What's Included</b>	Monitor panel, Stand riser, Stand base, VESA™ screw cover, Power cable, HDMI cable, Quick setup guide, Safety / Environmental / Regulatory Information	

<sup>1</sup>ComfortView feature reduces blue light emission and optimizes eye comfort.

<sup>2</sup>Advanced Exchange Service: Replacement part/unit dispatched, if needed, following completion of phone/online diagnosis.

Fee charged for failure to return defective unit. Availability varies. Other conditions apply.

<sup>3</sup>For a copy of the Limited Hardware Warranty, write Dell USA LP, Attn: Warranties, One Dell Way, Round Rock, TX 78682 or see Dell.com/warranty

<sup>4</sup>Enabled by Dell Display Manager

*Technical specifications subject to change without prior notice.*

Product availability varies by country. Please contact your Dell representative for more information.

Copyright 2021 Dell Inc. All rights reserved. Other trademarks or trade names may be used in this document to refer to either the entities claiming the marks and names or their products. Dell disclaims proprietary interest in the marks and names of others. Reproduction in any manner whatsoever without express written permission from Dell Inc. is strictly forbidden.