

Manufacturer Part #	Modern15A652
OS	Windows 10 Home
CPU	Core i7-1195G7
CPU Speed	2.9 - 5.0GHz
Chipset	-
Color	Carbon Gray
Screen Size	15.6" FHD, IPS-Level 60Hz 45%NTSCThin Bezel
Resolution	1920x1080 (16:9)
GPU	Intel® Iris® Xe
Keyboard	White backlight 84 Key
Audio	Nahimic 3 / Hi-Res Audio
Speaker	Speakers 2W * 2
Memory	16GB (8G*2) DDR4 2666MHz
HDD Capacity	512GB NVMe SSD
HDD Interface	NVMe
Optical Drive Type	-
WLAN	Intel Harrison Peak (2x2 802.11 ax)
Bluetooth	BT 5.1 (2x2)
Card Reader	Micro SD
Webcam	720p HD Webcam
USB	2x USB 3.2Gen 2; 1x USB 3.2 Gen1
Type-C Port	1x USB 3.2 Gen 2 Type C
Video Port	HDMI (supports 4K @ 30Hz)
Audio Port	Mic-in/Headphone-out Combo
AC Power Adaptor	65W
Battery Pack	3 cell (52Whr)
Dimension	14.05" x 9.20" x 0.67"
Weight	3.53 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)