



4K H.265 Wall Mount NVR with Facial Recognition and Smart Analytics

N8WNRE

8 Channel Facial Recognition Wall Mount NVR with 8 Built-in PoE Ports

N16WNRE

16 Channel Facial Recognition Wall Mount NVR with 16 Built-in PoE Ports

N32WNRE

32 Channel Facial Recognition Wall Mount NVR



Configurations

N8WNRE2TB	N16WNRE2TB	N16WNRE24TB	N32WNRE16TB
N8WNRE4TB	N16WNRE4TB	N16WNRE32TB	N32WNRE24TB
N8WNRE6TB	N16WNRE6TB	N32WNRE4TB	N32WNRE32TB
N8WNRE8TB	N16WNRE8TB	N32WNRE6TB	N32WNRE56TB
N8WNRE12TB	N16WNRE12TB	N32WNRE8TB	
N8WNRE16TB	N16WNRE16TB	N32WNRE12TB	

Key Features

EZ Wizards - For ease of use and setup

Camera: quickly discover and install all Speco IP cameras

Setup: for quick setup of general settings

Network: network setup and port forwarding

Record: quickly setup recording resolutions and recording type

EZ Search 2.0: Quickly find an event using time-sliced thumbnail images of your recordings with quick preview


Copy: quickly copy what you are playing onto a USB flash drive

EZ Mobile - easy mobile setup for viewing on desktop or mobile apps

- Real time recording up to 8MP resolution (4K) at 30fps
- H.265 compression - Store up to 2x more than H.264!
- 4K HDMI out and one VGA monitor output,
- N8WNRE: 1 SATA port for up to 14TB of storage max
N16WNRE: 2 SATA ports for up to 28TB of storage max
N32WNRE: 4 SATA ports for up to 56TB of storage max
(N32WNRE: additional storage via 2 eSATA ports)
- Facial Recognition and Comparison**
- Human and vehicle detection*
- Object and line crossing detection and alerts*
- Smart Search - Specify a region on the camera view and search on changes in that area*
- Free US-based DDNS and P2P services
- Remote viewing via web browser, Apple TV, Amazon Fire TV, or your mobile device
- Easy video exporting via USB
- Remote control included
- 5 year limited warranty¹

*with Speco Smart Analytic Cameras

**with Speco Facial Recognition Cameras



N16WNRE shown

Additional Features

- Find and install IP cameras on the local network without needing to locate the cameras manually
- Supports different recording types: Continuous, Motion, Analytics, and Sensor
- Create bookmark pins on playback for easy reference
- Instant playback for individual channels directly from the live view screen
- Customizable channel view placement
- Remote monitoring, recording, playback, configuration, upgrades, and PTZ control via the internet
- Simultaneous HDMI & VGA video output (N8WNRE & N16WNRE)
- Supports 2-way audio communication (speaker required)

INTEGRATED WITH
speco access



- Auto Live Camera Pop-Up
- View A Camera
- Event Tag



Optional Accessory



P16S18

18 Port Switch with 16 Port PoE
(for N32NRE)

¹Limited Warranty/Hard drives excluded. Check www.specotech.com for more details. iPhone is a trademark of Apple Inc., registered in the U.S. and other countries. Android is a trademark of Google Inc. Amazon's trademark is used under license from Amazon.com, Inc. or its affiliates. The terms HDMI and HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing LLC in the United States and other countries. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 7/12/21

Apps available from the following:



800-645-5516 • Fax: 631-957-9142 or 631-957-3880 • specotech.com

speco technologies

**Technical Specifications:**

4K H.265 Wall Mount NVR with Facial Recognition and Smart Analytics

Model			WNRE		
Video	Input	Max. IP Channels	8	16	32
		IP Camera	H.264/H.265 Auto Detection (Max. 8MP)		
	Output	Main Monitor	HDMI (Max. 4K) and VGA (Max. Full HD)		
		Sub Monitor	-		1 HDMI
Audio	Network Input		8 Ch. IPC audio input	16 Ch. audio input	32 Ch. IPC audio input
	2-way Audio		RCAx1		
	Local Output		RCAx1		
Recording	Encoding Resolutions		8MP/5MP/4MP/3MP/1080P/720P		
	Codec		H.264/H.265 (Auto Detection)		
	Max Frame Rate per Channel		Any Resolution @30fps		
	Recording Mode		Analytics/Continuous/Motion/Sensor/Schedule/Manual		
	Pre-Recording		Max. 5 seconds		
	Post Recording		Max. 10 minutes		
Search & Playback	Search		EZ Search, Motion, Specific Date/Time, Event, Museum, Bookmarks, Snapshots, Log		
	Simultaneous Playback		Max. 8 Ch.	Max. 8 Ch.	Max. 16 Ch.
	Smart Search		Highlighted color to display camera records in a certain period of time, different colors refer to different record events		
	Playback Resolutions		8MP/5MP/4MP/3MP/1080P/720P		
	Playback Functions		Play, pause, FF, FB, digital zoom, etc.		
Backup	Media		USB drive, Network		
	Format		JPG, AVI, ZIP (Player+Proprietary Data)		
Storage	HDD	Max Capacity of each HDD	14TB	14TB	14TB
		Internal SATA ports	1	2	4
	USB	Front	1 USB 2.0		
		Rear	1 USB 3.0		2 USBs: 1 USB 2.0, 1 USB 3.0
Alarm	Mode		Manual, sensor, motion, exception, intelligence		
	Input		8 Ch. local		
	Output		4 Ch. local		
	Linkage		Record/Snapshot/Preset/Email/Pop-up Window		
User I/F	Input Method		IR Remote, Mouse		
Network	Network Bandwidth		80Mbps	160Mbps	256Mbps
	P2P/Dynamic DNS		Free US-Based Speco P2P and DDNS Service		
	Network Protocols		TCP/IP, PPPoE, DHCP, DNS, UPnP, NTP, SMTP		
	Dual Network Card		-		Yes
	LAN 1		Recorder		
	LAN 2		-	-	Cameras
Network Access	Mobile		iOS/Android via Speco Blue App, SecureGuard® Client		
	Other Viewing Platforms		Apple TV and Amazon Fire TV		
	Web Viewer		Windows IE		
	VMS/CMS		SecureGuard®		
	Max. User Access		Max 10 users online (web client)		
Features	Digital Zoom		Live and Playback, Free Size		
	Smart Analysis		* **Facial Recognition, Crowd Density, People Counting, Object Detection, Tampering, Tripwire, Intrusion		
	S.M.A.R.T		Temperature, Power On Time, Bad Sectors and Health		
Power	Power Consumption		≤ 15W (without HDD)		
Environment	Operating Temperature		-4°F ~ 122°F(-10°C ~ 50°C)		
	Operating Humidity		10% ~ 90% humidity		
Dimensions	Unit		300mm x 248mm x 52mm (11.8" x 9.8" x 2.0")	380mm x 268mm x 52mm (15.0" x 10.6" x 2.0")	430mm x 453mm x 89mm (16.9" x 17.8" x 3.5")

* Does not have built in DHCP server

Please note that specifications and unit exterior design are subject to change without notification. Rev. 7/12/21

Apps available from the following:



800-645-5516 • Fax: 631-957-9142 or 631-957-3880 • specotech.com

