



Aruba Instant On AP11

Wi-Fi designed with small businesses in mind

Designed for small retail stores and home offices.

Small businesses are facing a number of challenges due to new and emerging technology, making it pretty overwhelming to keep up.

Mobile devices and cloud-based applications such as Microsoft Office 365 are changing the way you engage with customers, suppliers and staff. Since it's tough enough to set up a new payroll system or choose the most effective point of sale solution – we believe choosing the best Wi-Fi for your business should be simple.

Whether you own a small retail store or a boutique shop, your employees and customers are relying on the network for almost everything they do. And because Wi-Fi plays such a crucial role today, you need a purpose-built solution that keeps your business on the go. Aruba Instant On Access Points (APs) are easy to deploy and manage – with a quality look and feel at an attractive price point.

KEY FEATURES

Smart Mesh technology

802.11ac Wave 2, 2X2:2 MU-MIMO technology

Remote management and monitoring capability

Separate guest and employee Wi-Fi network

Mobile app and cloud portal

HIGHLIGHTS



Simplicity at its best

Wi-Fi that works right out of box
Easy-to-use mobile app for deployment and upkeep




Security you can count on

Wi-Fi that keeps business and visitor traffic separate
WPA2/WPA3 and Enhanced Open for secure network access



We've got you covered

Industry leading warranty and support
A customizable guest access page that shows off your brand



TECHNICAL SPECIFICATIONS

IN THE BOX

- Aruba Instant On AP11 Indoor Access Point
- Aruba Instant On AP11 Quick Start guide
- Ceiling rail mount clip
- Ethernet cable
- Solid surface mount clip

RADIOS

- Dual radio for simultaneous dual-band operation
- 5 GHz 802.11ac 2x2 MIMO for up to 867 Mbps wireless data rate, with Multi User MIMO support (Wi-Fi 5)
- 2.4 GHz 802.11n 2x2 MIMO for up to 300 Mbps wireless data rate (Wi-Fi 4)

INTERFACES

- Uplink Gigabit Ethernet port, with PoE-in support (802.3af)
- DC power connector (12V)
- Bluetooth Low Energy (BLE) radio
- LED status indicators (2)
- Reset/LED control button
- Kensington security slot

PHYSICAL SPECIFICATIONS

152mm x 152mm x 34mm, excluding mount accessories

Weight: 193g

POWER

Power over Ethernet (POE): 802.3af (class 3)

DC power (12V)

Note: Power sources are sold separately

ANTENNAS

Integrated down-tilt omni-directional antennas with maximum individual antenna gain of 3.3dBi in 2.4GHz and 5.8dBi in 5GHz

MOUNTING

The access point ships with a (black) mount clip to attach to suspended ceiling rails, and a (white) mount clip to attach to solid surfaces (wall/ceiling)

ENVIRONMENTAL & RELIABILITY

Operating temperature: 0° C to +40° C (+32° F to +104° F)

Humidity: 5% to 93% non-condensing

MTBF: 795khrs (91yrs) at +25° C

INDUSTRY CERTIFICATIONS

UL 2043 plenum rating

EN 60601-1-1 and EN 60601-1-2 (for deployment in medical environments)

Wi-Fi Alliance certified (WFA) 802.11ac with Wave 2 (Wi-Fi 5), WPA2, WPA3, Enhanced Open (OWE)

MANAGEMENT OPTIONS

Instant On mobile application (Android & iOS)

Cloud Portal: [Portal.ArubaInstantOn.com](https://portal.aruba.com)

WARRANTY & SUPPORT

Aruba Instant On 1 Year warranty with 24X7 phone support for first 90 days and chat support for the entire warranty period. Community support as long as you own the products

ORDERING INFORMATION

Aruba Instant On Indoor AP11 Access Points

| Part Number Points | Description | Comments |
|---|---|--------------------------------|
| R2W95A | Aruba Instant On AP11 (US) 2x2 11ac Wave2 Indoor Access Point | Add PoE or DC Power Source |
| R2W96A | Aruba Instant On AP11 (RW) 2x2 11ac Wave2 Indoor Access Point | Add PoE or DC Power Source |
| R2W97A | Aruba Instant On AP11 (EG) 2x2 11ac Wave2 Indoor Access Point | Add PoE or DC Power Source |
| R2W98A | Aruba Instant On AP11 (IL) 2x2 11ac Wave2 Indoor Access Point | Add PoE or DC Power Source |
| R2W99A | Aruba Instant On AP11 (JP) 2x2 11ac Wave2 Indoor Access Point | Add PoE or DC Power Source |
| R3J21A | Aruba Instant On AP11 (US) Indoor AP with DC Power Adapter and Cord (NA) Bundle | |
| R3J22A | Aruba Instant On AP11 (RW) Indoor AP with DC Power Adapter and Cord (EU) Bundle | |
| Power Options | | |
| R2X20A | Aruba Instant On 12V/30W Power Adaptor | Add AC power cord |
| R2X22A | Aruba Instant On 15.4W 802.3af PoE Midspan Injector | Add AC power cord |
| Power Options Continued Add 3-prong (C13) AC power cord for Power Adaptor/PoE Injector | | |
| JW113A | PC-AC-ARG Argentina 220V AC 10A 2-meter AC Power Cord | |
| JW114A | PC-AC-AUS Australian AC Power Cord | |
| JW115A | PC-AC-BR Brazil AC Power Cord | |
| JW116A | PC-AC-CHN China AC Power Cord | |
| JW117A | PC-AC-DEN Denmark 220V AC 10A 2-meter AC Power Cord | |
| JW118A | PC-AC-EC Continental European/Schuko AC Power Cord | |
| JW119A | PC-AC-IN India AC Power Cord | |
| JW120A | PC-AC-IL Israel 250V AC 10A 2-meter AC Power Cord | |
| JW121A | PC-AC-IT Italian AC Power Cord | |
| JW122A | PC-AC-JP Japanese AC Power Cord | |
| JW123A | PC-AC-KOR Korea AC Power Cord | |
| JW124A | PC-AC-NA North America AC Power Cord | |
| JW125A | PC-AC-SWI Switzerland 220V AC 10A 2-meter AC Power Cord | |
| JW126A | PC-AC-TW Taiwan AC Power Cord | |
| JW127A | PC-AC-UK UK AC Power Cord | |
| JW128A | PC-AC-ZA South Africa 250V AC 10A 2-meter AC Power Cord | |
| Mount Kits – Spares | | |
| JW044A | Instant On AP Ceiling Rail Mount Kit | Spare for what ships with AP11 |
| Q9U25A | Instant On AP Low Profile Basic Mount Kit | Spare for what ships with AP11 |