

SmartRack 12U Wall-Mount 2-Post Open Frame Rack, Hinged Front, Heavy Duty

MODEL NUMBER: SRWO12US2



Wall-mount open frame rack stores 12U of 19-inch rack equipment up to 22 inches deep and swings open for maximum accessibility.

Features

2-Post Wall-Mount Open Frame Rack Saves Valuable Floor Space

The SRWO12US2 open frame rack stores and organizes 12U of EIA-standard 19-inch rack equipment compatible with 2-post mounting. Designed for wall mounting, the rack saves space in network wiring closets, back offices and other secure areas with limited floor space where a locked enclosure is not required. The 2-post rack is made of heavy-duty steel with a durable black powder-coated finish. Maximum load capacity is 150 pounds (68 kilograms).

Hinged Front Provides Convenient Access to Cables and Equipment

The hinged front of the rack can be mounted to open to the left or the right, providing unrestricted access for installing, configuring and servicing cables and EIA-standard 19-inch rack equipment up to 22 inches deep, such as network switches and patch panels. The swinging front frame can be secured in position to prevent movement during equipment installation.

Easy Assembly and Equipment Mounting

Assemble this open frame rack on location with the included hardware. Wall-mounting holes are spaced 16 inches apart for standard wall stud placement with user-supplied fasteners. Vertical mounting rails with 12-24 threaded mounting holes accommodate equipment up to 22 inches deep. Rack spaces are numbered for easy reference.

Highlights

- 12U 2-post rack accommodates 19 in. rack equipment up to 22 in. deep
- Hinged front provides easy rear access to cables and equipment
- Keyhole mounting slots are spaced 16 in. apart to match standard wall stud placement
- Maximum load capacity is 150 lb.
- Assembly hardware is included

Package Includes

- SRWO12US2 12U Wall-Mount 2-Post Open Frame Rack, Hinged
- (2) Wall-mount bracket frames
- (2) Front rail assemblies
- Swinging door assembly
- (16) M6 hex bolts for assembly
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332264060
Device Compatibility	Network Switch; PDU; Patch Panel; Server; UPS
Rack Type	Open-Frame
PHYSICAL	
Color	Black



Maximum Device Depth (cm)	59.69
Maximum Device Depth (in.)	23.5
Maximum Device Depth (mm)	597
Rack Height	12U
Unit Dimensions (hwd / cm)	75.180 x 56.640 x 64.010
Unit Dimensions (hwd / in.)	29.600 x 22.300 x 25.200
Unit Weight (kg)	30.25
Unit Weight (lbs.)	66.700
Weight Capacity - Stationary (kg)	68
Weight Capacity - Stationary (lbs.)	150
Rack Depth	Shallow
Number of Vertical Mounting Rails	2
FEATURES & SPECIFICATIONS	
Built-in Cable Management	No
Extra Wide	No
STANDARDS & COMPLIANCE	
Approvals	EIA-310-D, IEC 60297-3-100, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>