




HP Engage 14 FHD No Stand and No VESA Monitor (42C50AA)



Specifications

Display size (diagonal)	35.56 cm (14")
Display size (diagonal)	14"
Panel technology	VA
Camera	Yes, 5MP
UPC number	(AB1) 197029810908; (AB2) 195908832393; (AB4) 195908832409; (ABG) 195908832416; (ABJ) 4573595655802; (ABT) 195908832423; (AC3) 195908832430; (AR6) 195908832447; (UUF) 195908832461

Additional specifications

Aspect ratio	16:9
Backlight type	Edge-lit
Bezel	4-sided micro-edge
Brightness	400 nits
Contrast ratio	800:1
Curvature	Flat
Detachable stand	Yes
Display area (imperial)	12.17 x 6.85 in
Display area (metric)	30.93 x 17.4 cm
Display features	On-screen controls; Touch enabled; Low blue light mode; Dual speakers (2W per channel); Anti-glare
Display scan frequency (horizontal)	30-80 KHz
Display scan frequency (vertical)	50-76 Hz
Ethernet	No
Flicker-free	No
Hardness	3H
Height adjustment range	No height adjust
Horizontal viewing angle	178°
Integrated privacy filter	No
Low blue light	Yes (Eyesafe® and TÜV certified)
Management Software	HP Display Center
Microphone	Yes
Native resolution	FHD (1920 x 1080)
Onscreen controls	Brightness; Information; Management; Power control; Input control; Menu control; Image; Color
Operating humidity range	20 to 80% non-condensing
Operating temperature range	5 to 35°C
Operating temperature range	41 to 95°F
Panel bit depth	8 bit
Physical security	None
Pixels per inch (ppi)	157 ppi
Resolution (maximum)	FHD (1920 x 1080 @ 60 Hz)

Resolutions supported	640 x 480; 720 x 400; 800 x 600; 1024 x 768; 1280 x 720; 1280 x 800; 1280 x 1024; 1366 x 768; 1440 x 900; 1600 x 900; 1600 x 1200; 1680 x 1050; 1920 x 1080
Screen treatment	Anti-glare
Speaker output power	2 x 1.5 W
Speaker type	2
Touch-enabled	Projected Capacitive technology
UNSPSC code	43211902
VESA mounting	100 mm x 100 mm (bracket included)
Vertical viewing angle	178°
pivot	No pivot
swivel	No swivel

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Dec 18, 2024 5:19 AM UTC+0000