

EZConvert Ex Pro MB987M2P-1B ICY DOCK®

1 x M.2 NVMe SSD to PCIe 3.0/4.0 x4 Adapter with Heat Sink & PCIe Bracket



Fits 1x PCIe Expansion Slot



Utilizing PCIe 3.0 & 4.0 Interface

Reduce cable clutter inside the system


PCIe 4.0 64Gbps **10x Faster!**

PCIe 3.0 32Gbps

SATA 6Gbps

Tool-less M.2 Drive Installation

Adjustable M.2 Locker



Compatible with Different length PCIe slots

Dual Function Metal Heatsink Cover

For maximum heat dissipation & protection



EZConvert Ex Pro MB987M2P-1B Features & Specs

- Fits 1 x M.2 PCIe NVMe SSD with all drive length including 2230 (30mm), 2242 (42mm), 2260 (60mm), 2280 (80mm), and 22110 (110mm)
- Use 1 x PCIe 3.0/4.0 x4 interface, also supports installation into PCIe 4.0 x8, and x16 slots
- Install into a single-width full-height expansion slot
Optional screw holes available for low profile PCIe bracket (not included)
- Low profile design allows for multiple bays to be installed side-by-side in a modular design
- Integrated heat sink and ample ventilation for excellent passive cooling
- Tool-less drive installation design for easy drive maintenance and system upgrading
- Active Power Technology (APT) saves power by shutting the device down when no drive is installed
- PCIe interface provides both power and data transfer, which ultimately reduce cable clutter
- Compatible with 2019+ Mac Pro PCIe expansion slots

*M.2 SSD not included

Model Number	MB987M2P-1B
Color	Black & Silver
Compatible Drive Type	1 x M.2 NVMe SSD
Support Drive Length	2230/2242/2260/2280/22110 (30-110mm)
Host Interface	PCIe 3.0/4.0 x4
Power Input	Via PCIe
Transfer Rate	PCIe 3.0 up to 32Gbps / PCIe 4.0 up to 64Gbps (Depending on SSD Speed)
Drive Cooling (Passive)	Aluminum heat sink with thermal pad
Structure / Material	Metal with partial ABS plastic
Number of Drives	1
Product Net Weight	125.2g
Dimension (W x H x D)	162.8 x 22 x 122mm
Package contents	Device, user manual, thermal pad,