



# PIXMA TR4720

## Wireless All-in-One Printer

### SPECIFICATIONS

PRINT	
Print Features	Auto 2-Sided (Duplex) Printing (Letter size, plain paper), Borderless Printing <sup>11</sup> , Canon PRINT Inkjet/SELPHY app <sup>2</sup> , Document Printing, Canon Print Service (for Android) <sup>12</sup> , AirPrint <sup>3</sup> , Mopria <sup>®</sup> Print Service <sup>4</sup> , Photo Printing, PIXMA Chat Print <sup>13</sup> , PIXMA/MAXIFY Cloud Link (Smart Device Only) <sup>2</sup> , Wireless Printing <sup>1</sup> , Template Print, Black Ink / Color Ink Only Printing
Printing Capability	Single Sided (Simplex) Printing
Print Speed (ESAT) <sup>10</sup>	4" x 6" Borderless Photo (PP-201): Approx. 65.0 Seconds Black Document (Letter/Simplex): Approx. 8.8 ipm Color Document (Letter/Simplex): Approx. 4.4 ipm
Number of Nozzles	Color: 960 / Pigment Black: 320/ Total: <b>1,280</b>
Print Resolution <sup>14</sup>	Up to 4800 x 1200 dpi
Paper Handling	Front Paper Tray
Paper Capacity	Input Capacity: 100 Sheets of Plain Paper <b>OR</b> 20 Sheets of 4" x 6" / 10 Sheets of 5" x 7" Photo Paper
Supported Paper/ Media Sizes	4" x 6", 5" x 7", 8" x 10", Letter (8.5" x 11"), Legal (8.5" x 14"), U.S. #10 Envelopes <b>Custom Size:</b> Width: 4" - 8.5" / Length: 6" - 26.6" <b>Borderless Printing<sup>11</sup>:</b> 4"x6", 5"x7", 8"x10", Letter (8.5"x11")
Media Compatibility	<b>Plain:</b> Plain Paper, Canon High Resolution Paper; <b>Glossy:</b> Photo Paper Pro Platinum, Photo Paper Plus Glossy II, Photo Paper Glossy; <b>Semi-Gloss:</b> Photo Paper Plus Semi-Gloss, Photo Paper Pro Luster; <b>Matte:</b> Matte Photo Paper; <b>Other (non-Canon):</b> Greeting Card, U.S. #10 Envelopes, Recycled paper and Chlorine-free paper can be used
Supported Media Thickness / Weight	Plain Paper: 64 - 105 gsm <b>OR</b> Canon Paper: Max. approx. 300 gsm (Canon PT-101 Media)
COPY	
Copy Features	4-on-1/2-on-1 Copy, Auto Document Feeder (ADF), Auto Exposure (AE) Copy, Borderless Copy, Collated Copy (ADF Only), Document Removal Reminder, Fit-to-Page, Frame Erase Copy (Flatbed Only), ID Card Copy, Multiple Copy (Up To 99 Pages), Preset Copy Ratio, Reduction/Enlargement (25% - 400%), Standard Copy, Two-Sided Copy
Copy Sizes	4" x 6", 5" x 7", Letter (8.5" x 11"), Legal (8.5" x 14")
Copy Media Compatibility	<b>Plain:</b> Plain Paper; <b>Glossy:</b> Photo Paper Pro Platinum, Photo Paper Plus Glossy II, Photo Paper Glossy; <b>Semi-Gloss:</b> Photo Paper Plus Semi-Gloss, Photo Paper Pro Luster; <b>Matte:</b> Matte Photo Paper; <b>Other (non-Canon):</b> Recycled paper and Chlorine-free paper can be used

# SPECIFICATIONS — PIXMA TR4720

<b>SCAN &amp; AUTO DOCUMENT FEEDER (ADF)</b>	
<b>Scan Features</b>	Auto Document Feeder (ADF), Auto Scan Mode <sup>15</sup> , Document Removal Reminder, Save to PC, Scan to Canon PRINT App <sup>2</sup> , Multi-Page PDF, Wireless Scanning <sup>1</sup>
<b>Scan Type</b>	Flatbed (ADF/Platen)
<b>Scanning Method</b>	Contact Image Sensor (CIS)
<b>Scanning Resolution<sup>16</sup></b>	600 x 1200 dpi (Optical)
<b>Maximum Color Scanning Bit Depth</b>	Grayscale: 16-bit/8-bit Color: 16-bit/8-bit Per Color
<b>Maximum Document Size</b>	Flatbed: 8.5" x 11.7" (Letter/A4) ADF: 8.5" x 14" (Legal/A4)
<b>ADF Sheet Capacity</b>	Letter Size: 20 Sheets Plain Paper Legal Size: 5 Sheets Plain Paper
<b>FAX</b>	
<b>Fax Features</b>	Speed Dial Utility (PC), Answering Machine Connectivity, Caller Rejection, Check RX Fax Info., Dial Search, Fax Reception Reject, Fax Number Re-Entry, Memory Transmission, Redial, Remote Reception, PC Fax available (Windows, Mac, B/W only)
<b>Fax Resolution Up to</b>	300x300 dpi (Black, Extra Fine) 200x200 dpi (Color)
<b>Modem Speed<sup>17</sup></b>	Max. 33.6 kbps (Automatic Fall Back)
<b>Transmission Speed<sup>18</sup></b>	Black: Approx. 3 sec Color: Approx. 1 min
<b>Memory Capacity<sup>19</sup></b>	Approx. 50 pages
<b>Speed Dialing</b>	<b>Coded Speed Dialing:</b> Max. 20 locations <b>Group Dialing:</b> Max. 19 locations
<b>Fax Print Size</b>	Letter (8.5" x 11"), Legal (8.5" x 14"), A4

# SPECIFICATIONS — PIXMA TR4720

CONNECTIVITY & SOFTWARE/APPS	
Connectivity	Hi-Speed USB Wi-Fi® (802.11b/g/n wireless networking, 2.4 GHz) <sup>1</sup> Wireless Direct Connection (Access Point Mode Only) Wireless Connect <sup>9</sup>
Wireless Information	Standard: IEEE 802.11 b/g/n Security: WPA-PSK (TKIP / AES), WPA2-PSK (TKIP / AES) Wireless LAN Frequency Band(s): 2.4 GHz Wireless Direct Connection Capable/ Wireless Connect <sup>9</sup> Capable: Yes
Smart Assistant & Automation Support	Amazon Alexa™ <sup>8</sup> Google Assistant™ <sup>8</sup>
OS Compatibility	<b>Windows:</b> <sup>20</sup> Windows® 10, Windows 8.1, Windows 7 SP1 <b>Mac:</b> <sup>21</sup> macOS 10.12.6 – 10.15 (Catalina) <b>Chromebook Compatible</b> <sup>22</sup> <b>Mobile Operating Systems:</b> <sup>23</sup> iOS®, iPadOS, Android™
Mobile Apps (iOS®/ Android™)	Canon PRINT Inkjet/SELPHY App <sup>2</sup> Canon Easy-PhotoPrint Editor App <sup>5</sup> Canon Creative Park App <sup>6</sup>
Software (Windows <sup>20</sup> /Mac <sup>21</sup> )	PIXMA TR4720 Wireless All-In-One Printer Driver IJ Scan Utility (Win/Mac) / IJ Scan Utility Lite (Mac Only) Easy-PhotoPrint Editor Software <sup>5</sup> Poster Artist Lite (Windows Only) <sup>7</sup> Canon Inkjet Smart Connect (Windows only) Easy-Layout Editor (Windows only)
GENERAL	
Display	2-Line LCD Display (Full Dot Matrix LCD)
General Features	Auto Power On/Off, 2 Cartridge FINE (Full-photolithography Inkjet Nozzle Engineering) Hybrid Ink System, Quiet Mode, Easy Setup with Canon PRINT Inkjet/SELPHY App <sup>1</sup> , Energy Star® Certified <sup>24</sup> , PIXMA Cloud Link <sup>2</sup> , Wireless Connect <sup>9</sup> , Printer Colors Available in Black and White, XL Ink Cartridge Support, Canon Printer Ink Subscription Plans <sup>27</sup> , Easy Ink Delivery
Supported Languages	<b>32 Languages Selectable:</b> Japanese, English (mm & inch), German, French, Italian, Spanish, Portuguese, Dutch, Danish, Norwegian, Swedish, Finnish, Russian, Ukrainian, Polish, Czech, Slovene, Hungarian, Slovakian, Croatian, Romanian, Bulgarian, Turkish, Greek, Estonian, Latvian, Lithuanian, Simplified Chinese, Korean, Traditional Chinese, Indonesian, Vietnamese
Power Information	Energy Efficiency: Energy Star® Certified <sup>24</sup> Auto Power On / Off Capable: Yes Input Voltage: AC 100 – 240 V, 50 / 60 Hz Power Consumption: 7W (0.8W Standby / 0.3W Off)
Warranty <sup>26</sup>	<b>1-Year Limited Warranty</b> with InstantExchange Program
Sound Management	<b>Quiet Mode:</b> Available <b>Noise Level:</b> Approx. 56.5 dB(A) (Plain Paper)
Operating Environment <sup>25</sup>	<b>Operating Temperature:</b> 41° - 95° F (5° - 35° C) <b>Operating Humidity:</b> 10 - 90% RH

# SPECIFICATIONS — PIXMA TR4720

INK INFORMATION	
Ink Types	PG-275 Pigment Black Ink CL-276 Dye Color Inks
Ink Cartridges & Fill Volume	PG-275 Black: 5.6 ml (Std.)   11.9 ml (XL) CL-276 Color: 6.2 ml (Std.)   12.6 ml (XL)
PRINTER INFORMATION	
Printer Dimensions (Closed)	17.2" (W) x 11.7" (D) x 7.5" (H)
Printer Dimensions (Paper Installed)	17.2" (W) x 16.2" (D) x 7.5" (H)
Printer Weight	12.7 lbs.
Box Contents	PIXMA TR4720 Wireless All-in-One Printer Set of Starter (PG-275/CL-276) Ink Cartridges RJ-11 Telephone/Modem Cable Power Cord Documentation

## DISCLAIMERS

**SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE. ALL VIEWSCREEN AND OUTPUT IMAGES ARE SIMULATED.**

- Wireless printing and scanning requires a working network with wireless 802.11b/g/n capability, operating at 2.4GHz. Wireless performance may vary based on terrain and distance between the printer and wireless network clients.
- Requires an Internet connection and the Canon PRINT Inkjet/SELPHY app, available for free on the App Store and at Google Play. Compatible with iPad, iPhone 3GS or later, and iPod touch 3rd generation or later devices running iOS 13.0 or later, and Android™ mobile devices running Android 5.0 or later. Your device must be connected to the same working network with wireless 802.11 b/g/n capability as your printer. Requires a compatible social media account and is subject to that social media account's Terms of Service. Certain exceptions may apply.
- AirPrint functionality requires a compatible iPad, iPhone, or iPod Touch device.
- Requires Android™ mobile device with Mopria® Print Service pre-loaded with that device. The Mopria® experience is also available with a download of the Mopria® Print Service from Google Play.
- The Easy-PhotoPrint Editor software requires an Internet connection and is compatible with the following operating systems; Microsoft Windows 10 (64-bit/32-bit), Microsoft Windows 8.1 (64-bit/32-bit), Microsoft Windows 7 SP1 (64-bit/32-bit), macOS High Sierra v10.13, macOS Sierra v10.12, Mac OS X El Capitan v10.11 and Mac OS X El Capitan v10.10.5. Minimum Windows and macOS/Mac OS X requirements are: 2GB of RAM and a monitor with 1024x768 resolution. The Easy-PhotoPrint Editor mobile application requires an Internet connection and the Easy-PhotoPrint Editor app v1.5.5, available for free on the App Store and at Google Play. Compatible with iPad Air 2 (2nd Generation), iPad Mini 4 and iPhone 6s or later devices running iOS 10 or later, and Android mobile devices running Android 5.x or later. Certain exceptions may apply. The following file formats are supported: JPEG, PNG, HEIF (devices running iOS 11 and mac OS v10.13 or later), DLP save data, Poster Artist export data, EasyPhoto+ export data, Easy-PhotoPrint Editor export data.
- Requires an Internet connection and the Creative Park app, available for free on the App Store and at Google Play. Requires an active 'Canon ID' available for free, and subject to 'Canon ID' Terms of Service. Visit [myid.canon](http://myid.canon) for more information. Certain exceptions may apply.
- PosterArtist Lite software v3.X is compatible with 64/32 bit versions of Microsoft® Windows® 10, Windows 8.1, Windows 7 and only compatible with select Canon PIXMA (released after July 2015), MAXIFY, imagePROGRAF and Océ® printers. Minimum computer system requirements: Pentium4 2.8GHz CPU or higher with 1GB RAM, 1024x768 pixel display and 5GB of system hard drive space.
- Requires an active smart assistant account linked and accompanying app enabled, the smart device and printer to be actively connected with permission to the Canon Inkjet Cloud Printing Center, and the required action(s), skill(s), or applet(s) available/enabled to the compatible printer. Voice commands can not be displayed as text on Amazon smart devices with screens.
- Requires a smart device with the Canon PRINT Inkjet/SELPHY app installed and connected to the desired active wireless network to complete cableless setup.
- Document print speeds are the averages of ESAT in Office Category Test for the default simplex mode, ISO/IEC 24734. Photo print speed is based on the default setting using ISO/JIS-SCID N2 on Photo Paper Plus Glossy II and does not take into account data processing time on host computer. Print speed may vary depending on system configuration, interface, software, document complexity, print mode, page coverage, type of paper used etc. Copy speeds are the average of sFCOT and sESAT, ISO/IEC 29183. Copy speed may vary depending on document complexity, copy mode, page coverage, type of paper used etc. and does not take into account warming up time. See [www.usa.canon.com/ipm](http://www.usa.canon.com/ipm) for additional details.
- Paper types NOT supported for borderless printing are as follows: Envelope, High Resolution Paper, T-Shirt Transfer and Photo Stickers. The maximum borderless printing size is 8.5"x11".
- Canon Print Service is a print plug-in for Android smart devices, which enables printing from Android mobile devices with Android v4.4.2 or later to many Canon printers via a Wi-Fi network. The plug-in does not work as a standalone app. Available for free at Google Play.
- This feature requires the printer to be connected with permission to the Canon Inkjet Cloud Printing Center (CICPC), an Internet connection, active 3rd party (social network or Cloud Storage) account, and a compatible Canon inkjet printer. Certain exceptions may apply.
- Resolution may vary based on printer driver setting. Color ink droplets can be placed with a horizontal pitch of 1/4800 inch at minimum.
- Auto Scan Mode is only available when scanning using a computer using the "IJ Scan Utility" or "IJ Scan Utility Lite" software.
- Optical resolution is a measure of maximum hardware sampling resolution, based on ISO 14473 standard. Optical resolution scan is available with TWAIN Driver only.
- The Public Switched Telephone Network currently supports fax modem speeds of 28.8 Kbps or lower, depending on telephone line conditions. Sending and receiving fax machines need to conform to ITU-T v.34 guidelines.
- Black & white document fax transmission speed is based on default setting using ITU-T No.1 chart. Color document fax transmission speed is based on default setting using Canon Color Fax Test Sheet. Actual transmission speed varies depending on document complexity, fax setting at receiving end, and line conditions etc.
- Page count is based on ITU-T No.1 chart or Canon FAX Standard Chart No.1. The number of pages able to be kept in memory will vary based on remaining memory capacity and document complexity.
- Operation can only be guaranteed on a PC with pre-installed Windows 10, Windows 8.1, Windows 7 SP1.
- Internet Connection required during software installation. For full compatibility macOS v10.13.6 or later is recommended.
- Functions and features may vary by printer model. Scanning requires Chrome OS 89 or later.
- Some functions may not be available with these Operating Systems. Please refer to manual or Canon website for details.
- As an ENERGY STAR® Partner, Canon U.S.A., Inc. has certified this printer as meeting the ENERGY STAR energy efficiency criteria through an EPA-recognized certification body.
- Print quality might be lower depending on the operating environment.
- Warranty programs are subject to certain conditions and restrictions. See [www.usa.canon.com/support](http://www.usa.canon.com/support) for details
- PIXMA Print Plan and Auto Replenishment Service sold separately and are subject to certain conditions and restrictions. See <https://www.usa.canon.com/print-plans> for details.

©2021 Canon U.S.A., Inc. Canon and PIXMA are registered trademarks of Canon Inc. in the U.S. and may be registered trademarks or trademarks in other countries. Microsoft, Windows, the Windows logo and Internet Explorer are trademarks or registered trademarks of the Microsoft group of companies in the U.S. and other countries. Apple, iPad, iPhone, and iPod touch are registered trademarks of Apple Inc. Android, Google Assistant, and Google Play are trademarks of Google Inc. The Mopria® word mark and the Mopria® Logo are registered and/or unregistered trademarks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. Amazon, Alexa, and all related logos are trademarks of Amazon.com, Inc. or its affiliates. Wi-Fi is a registered trademark of the Wi-Fi Alliance. All other product and brand names are trademarks of their respective owners. As an ENERGY STAR® partner, Canon U.S.A., Inc. has certified this product as meeting the ENERGY STAR energy efficiency criteria through an EPA-recognized certification body.