


X1000-4K - ULTRA-SHORT THROW 4K UHD PROJECTOR WITH 2400 LED LUMENS, USB C, BLUETOOTH SPEAKERS AND WI-FI

Key Features


- True 4K Ultra HD Resolution
- Ultra-Short Throw Projection
- Cinema SuperColor+™ Technology
- Advanced LED Light Source
- 40W Harman Kardon Soundbar
- Wi-Fi/Bluetooth connectivity




60 - 150 in. / 1.78 - 3.81 m (diagonal)
DISPLAY



PANEL



3840 x 2160
RESOLUTION



 SOUND BY 

Product Description

Combining stunning true 4K resolution with WiFi-enabled streaming functionality, the ViewSonic® X1000-4K projector delivers a cinematic experience with the ease and convenience of ultra-short throw projection. With a 0.25 ultra-short throw lens, this home theater projector can be placed just inches away from a wall or screen, and project an immersive image up to 100". Whether simply placed on a media stand or mounted to the ceiling, this projector delivers vivid and razor-sharp images thanks to 2,400 lumens of brightness, Rec. 709 compatibility, and stunning true 4K Ultra HD 3840 x 2160 resolution. An integrated 40W Harman Kardon customized soundbar delivers room-filling audio perfect for music and movies. The X1000-4K can also be utilized as a Bluetooth soundbar, or connected to a subwoofer to create a 2.1 audio system.

Specifications

More Information	
UPC	766907001655
Light Source	DLP LED
Display Resolution	4K (3840x2160)
Display Resolution	3840 x 2160
Brightness (Lumens)	2,400 LED
Screen Size	60 - 150 in. / 1.78 - 3.81 m (diagonal)
Throw Distance	0.159m-0.657m (100" @ 0.379m)
Throw Ratio	0.25
Keystone	Vertical (+/- 14°)
Lens	Fixed Zoom
Light Source (watt)	RGBB LED
Light Source Life, Normal (hours)	30000
Color Depth	1.07 Billion Colors
Dynamic Contrast Ratio	3,000,000:1
Aspect Ratio	16:10
Input Lag	37ms
Frequency Horizontal	15K-135KHz
Frequency Vertical	23-120Hz
PC Resolution (max)	3840 x 2160
PC Resolution (min)	640 x 480
Mac® Resolution (max)	3840 x 2160
Mac® Resolution (min)	640 x 480
USB 2.0 Type A	4
USB 3.0	2
USB 3.1 Type C	1
Ethernet LAN (RJ45)	1
SPDIF Audio Out	1
3.5mm Audio Out	2
3.5mm Audio In	1
HDMI 2.0 (with HDCP 2.2)	3
Micro USB	1
Internal Speakers	40W (20W Cube x 2)
Voltage	100-120V +/- 10%, 50/60Hz

Consumption (typical)	200W
Stand-by	<0.5W
Physical Controls	Keypad, Power key
On Screen Display	Display, Image, Power Management, Basic, Advanced, System, Information (See user guide for full OSD functionality)
Temperature	32-95° F (0 - 35° C)
Kensington Lock Slot	1
Net (lbs)	20.8
Gross (lbs)	28.8
Net (kg)	9.4
Gross (kg)	13.1
Packaging (in.)	38.3 x 16.1 x 12.0
Physical (in.)	29.8 x 11.5 x 6.7
Packaging (mm)	973.0 X 408.0 X 306.0
Physical (mm)	757.0 x 291.0 x 169.0
Regulations	FCC, cTUVus, ROHS
Package Contents	X1000-4K projector, power cable, USB-C cable, remote control(w/ backlit), Quick Start Guide
Warranty	Three-year limited warranty on parts and labor, 1-year limited warranty on lamp, 1st year free Express Exchange® service. (One year Express Exchange Service requires product registration).
Classification	Discontinued

UPC: 766907001655



Contact Sales

ViewSonic.com

888.881.8781

email:

salesinfo@viewsonic.com