

14-inch Mobile Thin Client

11th Gen Intel® Core™ i3 with Windows® 10 IoT Enterprise



KEY FEATURES

14ZT90P-G.AM33U1

- Intel Core i3-1115G4 DC (3.0 GHz Turbo up to 4.1GHz)
- 8 GB System Memory
- 256 GB NVMe SSD
- 14" WUXGA (1920x1200) IPS Display
- Windows 10 IoT Enterprise LTSC
- TPM (Trusted Platform Module) Security
- HD Webcam with Dual Microphone
- Full Size Backlit Keyboard
- Ultra-thin less than 0.7" Thickness
- Extremely light 2.2 lbs

Combining a tough, lightweight magnesium alloy body with an ultra-thin form factor, excellent performance and great battery life, this mobile thin client is the ultimate tool for the business traveler. This LG gram mobile thin client has been equipped with 11th Gen Intel processors, a 72 Wh lithium-Ion battery and is pre-loaded with Windows 10 IoT Enterprise LTSC.

Light Weight

The LG gram 14-inch laptop offers awesome screen size without the weight. With gram's innovative design and construction, this laptop weighs only 2.2 pounds, so it's easy to take anywhere.



Tough & Low Profile

The sleek metal alloy body of the LG gram combines advanced nano carbon with magnesium to create a light weight yet durable housing for the computer that's still beautifully thin at 0.66 inches thick.

Multiple Ports

Connect it all with gram's host of popular ports. Gram's HDMI port lets gram connect easily to virtually all types of high-definition displays.



Long-Lasting Battery

Portability is a function of battery life in addition to size and weight, and this LG gram has been designed to keep going with hours of power to hit deadlines and keep streaming long after others have quit.

14ZT90P-G.AM33U1 Specifications

Processor	i3-1115G4 DC (3.0 GHz, Turbo up to 4.1 GHz, Smart Cache 6 MB, 28 W)
Graphics	Intel UHD Graphics
Operation System	Windows 10 IoT Enterprise LTSC (Value SKU)
System Memory	8 GB (LPDDR4x 3733 MHz), Dual Channel
Display	35.5cm (14.0") WUXGA (1920x1200) IPS LCD
Storage	NVMe 256 GB
Wireless	Intel Wireless-AX201 (802.11ax, 2x2, BT Combo)
Bluetooth	5.1
Webcam	HD Webcam with Dual Microphone
Audio	HD Audio
Speaker	Stereo Speaker (Max. 2.0 W x 2)
Security	SSD Security, Finger Print, TPM
Keyboard	Backlit 79-key Keyboard
Touch Pad	Precision Touch Pad (Scroll & Gesture Function)
MMC Slot	UFS / Micro-SD
Connectivity	USB 3.2 Gen 2x1 (x2) USB 4 Gen 3x2 Type C (x2, USB PD & TBT4) 3.5mm Headphone Out HDMI, Slim Kensington Lock
Battery	72 Wh (Li-Ion)
AC Adapter	65W Power Supply
Button	Power Button with Finger Print Sensor
LED Indicators	PWR, DC-In
Dimension	12.3 x 8.5 x 0.66 in 313.4 x 215.2 x 16.8 mm
Weight	2.2 lbs (999 g)
Color	Silver
Preinstalled Software	<ul style="list-style-type: none"> - LG Easy Guide - LG Cloud Agent - LG Cloud Panel Software - LG Cloud Launcher Software - VDI Client : Citrix Workspace, VMware Horizon Client, PCoIP Client - LG Recovery - LG Cloud Device Manager Software

* Specifications are subject to change without notice, so please reach LG salesteam to ensure before ordering.