

# ThinkVision E24-28 62C8MAR4US

## Product

ThinkVision E24-28

## Machine Type

62C8

## Region

LA, NA

## Display Size

23.8"

## View Area

527.04x296.46 mm

## Panel

In-Plane Switching

## Aspect Ratio

16:9

## Resolution

1920x1080

## Pixel Pitch

0.2745 x 0.2745 mm

## Dot / Pixel Per Inch

92 dpi

## View Angle (H / V)

178 / 178

## Pixel Response Time

4 ms (Extreme mode) / 6 ms (Typical mode)

## Refresh Rate

60 Hz

## Brightness

250 nits

## Contrast Ratio

1000:1

## Color Gamut

72% NTSC

## Anti-glare

Yes

## Multiple Input

HDMI, DP, VGA

## USB Port

None

## Camera

None

## Microphone

None

## Speaker

2x 1.5W

## Power Consumption (Typical / Maximum)

18W / 24W

## Power Adapter

Integrated

## Stand

Tilt, Swivel, Pivot, Height Adjust Stand

## Color

Raven Black

## Side Bezel Width

3.1 mm

## Dimensions with Stand (HxWxD)

462.5x541.8x178.6 mm / 18.21x21.33x7.03 inches

## Weight (Including Stand)

4.8 kg / 10.58 lbs.

## Monitor cable

HDMI

## ENERGY STAR

Yes

## TCO

TCO 8.0

## EPEAT

Silver

## TÜV Rheinland Low Blue Light

None

## TÜV Rheinland Eye Comfort

Yes

## TÜV Rheinland Eyesafe Display

None

## TÜV Rheinland Flicker Free

None

## Base Warranty

3-year

## Operating System Support

Support Windows 7, Windows 10

## Sync Technology

None

## Tiny Support / CPU / Platform

Tiny Support / None / None

## Ethernet / Bluetooth / Wireless

None / None / None

## Touch Screen / Digitizer Pen / Battery

None / None / None

## Display Ram / Storage / Card Slot

None / None / None

## EAN / UPC / JAN

0195477929203

## Announce Date

2021-07-15



[WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2021. All rights reserved.



# ThinkVision E24-28

## DISPLAY

Panel Size	23.8-inch
Screen Dimensions	534.44 mm x 303.66 mm
Panel Type	In-Plane Switching
Active Area	527.04 mm x 296.46 mm
Backlight	WLED

Aspect Ratio	16:9
--------------	------

Resolution	1920 x 1080
------------	-------------

Pixel Pitch	0.2745 mm x 0.2745 mm
-------------	-----------------------

Dot/Pixel Per Inch (DPI/PPI)	93
------------------------------	----

Viewing angle (H x V @ CR 10:1)	178° / 178°
---------------------------------	-------------

Response Time	4ms (Extreme mode) 6ms (Normal mode)
---------------	---

Refresh Rate	60 Hz
--------------	-------

Brightness (typical)	250 cd/m <sup>2</sup>
----------------------	-----------------------

Contrast Ratio (typical)	1000:1
--------------------------	--------

Dynamic Contrast Ratio (typical)	3M:1
----------------------------------	------

Color Gamut	72% NTSC (CIE 1931)
-------------	---------------------

Color Support (typical)	16.7 Million
-------------------------	--------------

Anti-glare	Yes
------------	-----

\* Optional support.

Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: 5 Gbit/s for USB 3.2 Gen 1; 10 Gbit/s for USB 3.2 Gen 2 & 20 Gbit/s for USB 3.2 Gen2x2.

© 2020 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

## CONNECTIVITY

Video Signal	1 x HDMI 1.4 1 x DP 1.2 1 x VGA
--------------	---------------------------------------

## MULTI-MEDIA

Integrated Speakers	Yes (2 x 1.5W)
---------------------	----------------

## POWER

Power Consumption (typ./max)	18W / 24W
------------------------------	-----------

Power Consumption Sleep/Off Mode	< 0.5W
-------------------------------------	--------

Power Consumption Switch Off-Mode	< 0.5W
--------------------------------------	--------

ENERGY STAR Power Consumption (P <sub>on</sub> /E <sub>TFC</sub> )	13W / 41kWh
--	-------------

Power Supply	Internal
--------------	----------

Voltage Required	AC 90 to 264 V (47-63 Hz)
------------------	---------------------------

## MECHANICAL

Tilt Angle (front/back)	-5° / 22°
-------------------------	-----------

Swivel Angle (left/right)	-360° / 360°
---------------------------	--------------

Lift (max range)	155 mm
------------------	--------

Pivot	-90° / 90°
-------	------------

VESA Mount Capability	Yes (100 x 100 mm)
-----------------------	--------------------

ThinkCentre Tiny Support*	Yes, by Sandwich Mounting Kit (PN: 4XHONO4098)
---------------------------	--

Kensington Lock Slot	Yes
----------------------	-----

Bezel Color	Raven Black
-------------	-------------

Bezel Width (side)	3.1 mm
--------------------	--------

Bezel Width (top/bottom)	3.1 / 20.9 mm
--------------------------	---------------

## DIMENSION

Size Packed (D x H x W, mm/inch)	145.0 x 397.0 x 638.0 mm 5.71 x 15.63 x 25.12 inches
----------------------------------	---

Size Unpacked w/ Stand (D x H x W, mm/inch) (lowest position)	178.6 x 317.1 x 541.8 mm 7.03 x 12.48 x 21.33 inches
---	---

Size Unpacked w/ Stand (D x H x W, mm/inch) (highest position)	178.6 x 462.5 x 541.8 mm 7.03 x 18.21 x 21.33 inches
--	---

Size Unpacked w/o Stand (head only) (D x H x W, mm/inch)	41.7 x 326.4 x 541.8 mm 1.64 x 12.85 x 21.33 inches
--	--

Weight Packed (kg/lbs.)	5.70 kg / 12.57 lbs.
-------------------------	----------------------

Weight Unpacked (kg/lbs.)	4.80 kg / 10.58 lbs.
---------------------------	----------------------

Weight (Monitor Head Only) (kg/lbs.)	3.10 kg / 6.83 lbs.
--------------------------------------	---------------------

## CERTIFICATION

ENERGY STAR Certification	Yes
---------------------------	-----

CCC
-----

TCO
-----

TCO Edge	2.0
----------	-----

EPEAT
-------

RoHS (2011/65/EU)
-------------------

Windows Certification	Windows 7, Windows 10
-----------------------	-----------------------

China Energy Efficiency Standard	Tier 1
----------------------------------	--------

TÜV Rheinland Eye Comfort
---------------------------



# ThinkVision E24-28

Lenovo

