


4XEM Nylon Braided USB-C to C 40 Gigabit 1.5 FT (Half Meter) Cable

4XEM Part- 4XUSB40GBRD050CM



Looking for a high-quality USB-C to C cable that can handle all your data transfer and charging needs? Look no further than the 4XEM Nylon Braided USB Type C to Type C 40 Gigabit 1.5 FT Cable.

This cable is built to last, with a durable nylon braided exterior that can withstand even the toughest wear and tear. And with a length of 19 inches, it's the perfect length for use at your desk or on-the-go.

But what really sets this cable apart is its incredible speed. With 40 gigabit transfer speeds, and being E-marked for 100W of power, it's one of the fastest USB-C to C cables on the market. That means lightning-fast data transfers and ultra-quick charging times, so you can get back to using your devices in no time.

Whether you're a power user who needs the fastest possible speeds, or just someone who wants a reliable cable that won't let you down, the 4XEM Nylon Braided USB-C to C 40 Gigabit Half Meter Cable is the perfect choice. So why wait? Get yours today and experience the ultimate in USB-C to C connectivity!

4XEM Products Are Available At Your Favorite Online Retailers

WWW.4XEM.COM

Contact Todd Schaus 4XEM sales Rep
1-866-999-4936 Ext.104 tschaus@4xem.com



Features

- **High-Speed Transfer:** With 40 gigabit transfer speeds, this cable is designed to provide lightning-fast data transfers.
- **Fast Charging:** This cable supports fast charging, E-Marked to power up to 100W charging, so you can quickly charge your USB-C devices.
- **Durable Design:** The nylon braided exterior is built to last, providing a sturdy and reliable cable that can withstand everyday wear and tear.
- **Perfect Length:** At 1.5 FT (19in) or half a meter long, this cable is the perfect length for use at your desk, or on-the-go.
- **Universal Compatibility:** This cable is designed to work with a variety of USB-C devices, making it a versatile choice for all your connectivity needs.
- **Sleek Design:** The cable features a sleek and modern design that will look great with any device.
- **Easy to Use:** Simply plug in and start using your devices right away, with no complicated setup or configuration required.

Application

- Home
- Connections
- Office
- Charging & Data Transfer

4XEM Products Are Available At Your Favorite Online Retailers



**DATA SHEET**

Warranty Information	Warranty	Lifetime
Hardware	Operating Mode Direction Industry Standards E-Marker Power Rating	Passive Bidirectional USB4 20V, 5A (100W)
Connector(s)	Connector A Connector B	USB Type-C USB Type-C
Performance	Data Transfer Rate Video Support	40 Gbps Yes
Certifications	Certifications	N/A
Physical Characteristics	Colour Connector Plating Connector Style Plug Material Cable Jacket Type	Black Nickel Straight Aluminum Nylon Braid
	Cable OD Cable Length Weight of Product	0.20 in [5.1 mm] 19.69 in [0.50 m] 0.85 oz [24 g]
Packaging Information	Package Height Package Width Package Length Shipping (Package) Weight	8.25 in [209.6 mm] 6.75 in [171.5 mm] 0.47 in [11.9 mm] 0.99 oz [28 g]
What's in the Box	Included in Package	1x 19 in/0.5m USB4 Cable
Notes	Notes	40 Gbps is the theoretical maximum bandwidth. Actual performance may vary depending on various factors including but not limited to connected computer hardware, connected peripheral, cable length, cable quality, and data overhead.

* Product appearance and specifications are subject to change without notice.
* Weights and measurements are approximate.

4XEM Products Are Available At Your Favorite Online Retailers

WWW.4XEM.COM

Contact Todd Schaus 4XEM sales Rep
1-866-999-4936 Ext.104 tschaus@4xem.com

