

GBP24V18AH

24V 2U External Battery Pack for GBB1000N

- Extend battery runtime when used IOGEAR Online UPS system.



Secure, Reliable Expandable Power Solution for All Server Needs

IOGEAR External Battery Pack GBP24V 18AH is a high-performance expandable rackmount external battery pack solution for the IOGEAR Online UPS Battery Back Up -GBB1000N. The battery pack provides extended battery runtime for critical server rack configurations that support voice, data, medical and industrial network applications. An included daisy chain connector to enable the connection of additional compatible 24V external battery packs to primary Online UPS battery back system.

Expandable battery solution for GBB1000N

Daisy chain for increased runtime



Requirements

Work with IOGEAR Online UPS GBB1000N

Package Contents

- 1x Battery External Pack - GBP24V18AH
- 1x Rack Mounting Kit
- 1x Rail Slide Kit
- 1x Battery cable
- 1x Tower Extend Stand

Specifications

Function	GBP24V18AH	Dimensions	GBP24V18AH
Electrical		Unit Dimensions	
Input Voltage	24V	Height	3.5 in. (8.9 cm)
Output Voltage	24V	Length	15 in. (38 cm)
Maximum Output Current(Total)	50A Max	Width	17.3 in. (44 cm)
Battery		Master Carton	
Battery Type	Sealed Lead-Acid	Height	9.5 in. (24.2 cm)
Size	12V/9Ah	Length	23.5 in. (59.7 cm)
Battery Quantity	4	Width	19.75 in. (50.2 cm)
		Master Carton Qty.	1
		Weight	
		Master Carton Wt.	45.6 lb. (20.74 kg)
		Unit Wt.	37.6 lb. (17.1 kg)