

GBP72V18AH

72V 2U External Battery Pack for GBB3000N



- Extend battery runtime when used IOGEAR Online UPS system.

Secure, Reliable Expandable Power Solution for All Server Needs

IOGEAR External Battery Pack 72V 18Ah is a high-performance expandable rackmount external battery pack solution for the IOGEAR Online UPS Battery Back Up 3000LV (GBB3000N). The battery pack provides extended battery runtime for critical server rack configurations that support voice, data, medical and industrial network applications. An included daisy chain connector to enable the connection of additional compatible 72V external battery packs to primary Online UPS battery back system.

Expandable battery solution for

Daisy chain for increased runtime



Requirements

Work with IOGEAR Online UPS GBB3000N

Package Contents

- 1x Battery External Pack - GBP72V18AH
- 1x Rack Mounting Kit
- 1x Rail Slide Kit
- 1x Battery cable
- 1x Tower Extend Stand

Specifications

Function	GBP72V18AH	Dimensions	GBP72V18AH
Electrical		Unit Dimensions	
Input Voltage	72V	Height	3.5 in. (8.9 cm)
Output Voltage	72V	Length	23.6 in. (60cm)
Maximum Output Current(Total)	50A Max	Width	17.3 in. (44 cm)
Battery		Master Carton	
Battery Type	Sealed Lead-Acid	Height	9.75 in. (24.8 cm)
Size	12V/9Ah	Length	29.5 in. (74.9 cm)
Battery Quantity	12	Width	23.5 in. (59.7 cm)
		Master Carton Qty.	1
		Weight	
		Master Carton Wt.	103 lb. (46.5Kg)
		Unit Wt.	90.8 lb. (41.2Kg)