




FEATURES

- 27-Inch Screen Size / 1920 x 1080 Full HD Resolution
- Long Acting **Antibacterial** Screen
- **SGS** Report Pass the Value of **Antimicrobial** Activity
- Prevent **95%** of **Viruses** and **Bacteria**
- **HDMI / DVI-D / VGA / USB / Audio** Connectors
- **10-Point PCAP** Projected Capacitive Touch Technology
- **IP65** Waterproof / **Dust Proof** / **Vandal Proof**
- Surface **MoHs7** **Anti-Scratch** technology
- **LED** Backlight Unit
- **3-Year** Warranty



SPECIFICATIONS

1080P
FULL HD

DISPLAY		AB27ZD-OV-45P0	
Screen Size	27 In		
Resolution	1920 x 1080		
Active Area(mm)	597.6 (H) x 336.15 (V)		
Backlight	LED		
Aspect Ratio	16 : 9		
Viewing Angle	178° / 178°		
Response Time	12ms		
Brightness	250cd/m ²		
Contrast Ratio	1000 : 1		
Color Depth	16.7M		
INTERFACE			
HDMI	1		
DVI	1		
VGA	1		
Audio Out	1		
USB	1		
TOUCH TECHNOLOGY			
Type	Projected Capacitive (PCAP)		
Points	10-Point		
Interface	USB (B-Type)		
SPECIAL FEATURES			
Glass	Prevent Bacteria		
Waterproof	IP65		
Dust Proof	Yes		
Vandal Proof	Yes		
CABINET			
Material	Metal		
POWER			
Input Voltage	12V DC +/- 5%		
Electrical Ratings	AC 100V ~ 240V, 50/60Hz		
TEMPERATURE			
Operating	32° F ~ 122° F (0° C ~ 50° C)		
Storage	-4° F ~ 140° F (-20° C ~ 60° C)		
DIMENSIONS (WxHxD)			
Inch (in)	25.60 x 15.29 x 1.81		
Millimeter (mm)	650.4 x 388.4 x 46.0		
WEIGHT			
Net Weight	23.14 lbs (10.5 kg)		
VESA™			
Mount Size (mm)	75 x 75 / 100 x 100		

Specifications subject to change without any notice

AB27ZD-OV-45P0

Gvision's most advanced antibacterial monitor can be used in hospitals, restaurants or anywhere else where human hygiene is a concern, the AB Series destroys bacteria and harmful microorganisms on contact. It is chemically bonded to the surface, making it a permanent part of the touch-screen and allowing it to remain functional even after long-term use. SGS Standards Technical Services tested and pass the value of antimicrobial activity against common bacteria.

DIMENSIONS

Unit: Inch

