


# C43BI-AC-4000

Gvision's 43" 4K UHD CCTV security monitors are design for 24 / 7 / 365 operating. It support 3 HDMI, and 1 DisplayPort. C43BI security CCTV monitor is featured Quad Video Splitter, Anti-Pixel burn technology, display superior quality of picture, and flick free screen.

## DIMENSION

Unit: Inch



## FEATURES

- 43-Inch Screen Size / 3840 x 2160 **4K UHD** Resolution
- Video Inputs: **HDMI / DisplayPort (DP)**
- **5W x 2** Built-In Audio
- Built-In **Quad Video Splitter** to Split the Screen into 4, **PIP/PBP, Auto Wake-Up, Anti-Burn Technology**
- **300cd/m<sup>2</sup>** High Brightness
- **LED Backlight Unit**
- **24/7 Operation Commercial CCTV Monitor**
- **3-Year Warranty**

## SPECIFICATIONS

**4K**  
**ULTRA HD**

| DISPLAY                    | C43BI-AC-4000                                              |
|----------------------------|------------------------------------------------------------|
| Screen Size                | 43 In                                                      |
| Resolution                 | 3840 x 2160                                                |
| Backlight                  | LED                                                        |
| Aspect Ratio               | 16 : 9 / 4 : 3                                             |
| Viewing Angle              | 178° / 178°                                                |
| Response Time              | 5ms (G2G)                                                  |
| Brightness                 | 300cd/m <sup>2</sup>                                       |
| Contrast Ratio             | 1000:1                                                     |
| Color Depth                | 1.07 Billion Colours                                       |
| INTERFACE                  |                                                            |
| HDMI 1.4 In                | 2                                                          |
| HDMI 2.0 In                | 1                                                          |
| DisplayPort 1.2 (DP) In    | 1                                                          |
| Audio Out                  | 1                                                          |
| AUDIO                      |                                                            |
| Speaker                    | 5W x 2                                                     |
| FEATURES                   |                                                            |
| <b>Quad Video Splitter</b> | Yes                                                        |
| PIP/PBP                    | Yes                                                        |
| Anti Picture Burn-in       | Yes                                                        |
| Auto Wake Up               | Yes                                                        |
| Remote Controller          | Yes                                                        |
| Plug & Play                | Yes                                                        |
| CABINET                    |                                                            |
| Color                      | Black                                                      |
| POWER                      |                                                            |
| Consumption                | < 110W                                                     |
| Electrical Ratings         | AC 100V ~ 240V, 50/60Hz                                    |
| TEMPERATURE                |                                                            |
| Storage                    | -22° F ~ 158° F (-30° C ~ 70° C)                           |
| Operating                  | -4° F ~ 122° F (-20° C ~ 50° C)                            |
| DIMENSIONS (WxHxD)         |                                                            |
| Inch w/ Stand (in)         | 38.22 x 24.5 x 8.36                                        |
| Millimeter w/ Stand (mm)   | 970.8 x 622.3 x 212.4                                      |
| WEIGHT                     |                                                            |
| Net Weight                 | 15.4 lbs (7.0 Kg)                                          |
| VESA™                      |                                                            |
| Mount Size (mm)            | 200 x 200                                                  |
| ACCESSORY                  |                                                            |
| Accessories                | Signal Cable / Remote Contol / Power Cable / User's manual |

*Specifications subject to change without any notice*