

PERFORMANCE

Display Size
27"

View Area
596.74x335.7 mm

Panel
VA

Aspect Ratio
16:9

Resolution
2560x1440

Pixel Pitch
0.2331x0.2331 mm

Dot / Pixel Per Inch
109 dpi

View Angle (H / V)
178 / 178

Response Time
4 ms (Extreme mode) / 6 ms (Typical mode)

Color Support
16.7 Million

Refresh Rate
75 Hz

Brightness
350 nits

Contrast Ratio
4000:1

Color Gamut
99% sRGB

Anti-glare
Yes

Curvature
None

Camera
Lenovo® LC 50 support

Microphone
None

Speakers
3Wx2

Power Consumption (Typical / Maximum)
28W / 52W

Power Adapter
Integrated

Touchscreen
None

Smart System

None

DESIGN

Stand
Tilt Stand

Case Color
Raven Black

Side Bezel Width
2 mm

Dimensions with Stand (HxWxD)
476.6x614.5x174.9 mm / 18.76x24.19x6.89 inches

Weight (Including Stand)
4.8 kg / 10.5 lbs.

ThinkCentre® M Series Support
None

CONNECTIVITY

USB Port
None

Video Connector
1x HDMI® 1.4, 1x DP 1.2

Network Connectivity
None

SERVICE

Base Warranty
1-year

CERTIFICATIONS

Environmental Certification
RoHS

Ergonomic Certification
Eyesafe® Display, TÜV Rheinland® Eye Comfort

Sync Technology
AMD FreeSync™

SOFTWARE

Operating System
Support Windows® 7, Windows 10

ACCESSORIES

Video Cables
HDMI cable

MODEL

Announce Date : 2021-08-13

EAN / UPC / JAN : 0195713801379 / 195713801379 / None



Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.


Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



ThinkCentre Tiny VESA Mount II

4XFON03161

The ThinkCentre Tiny VESA Mount II is a unique design specific to house the Tiny PC while featuring the universal VESA mount configuration. The VESA standard enables this mount to attach to anything that is VESA comp...



Kensington MicroSaver 2.0 Cable Lock from Lenovo

4XEON80914

Protect your device. Lenovo offers the latest standard in device security - the MicroSaver 2.0 Cable Lock From Lenovo. Engineered to be the smallest, strongest lock for laptops and other devices, the MicroSaver 2.0 re...

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference