



IK-82-SA

IK-82-SA Stand Alone Keyboard

New! The sealed, rugged IK-82-SA is a rugged, fully sealed, stand-alone keyboard is fully mountable and it is compatible with many brands of tablets and terminals. We currently have layouts for English, French Canadian and UK. Other language layouts may be available, at certain minimum order quantity — simply contact us for details.

512-837-0283

Specifications: IK-82-SA

- IP65 rated – protects from spills and easy to wipe down and disinfect with hospital-grade methods including 99.9% Isopropyl Alcohol or a bleach/water solution of 10% to 70% bleach
- Full-size QWERTY keyboard
- 4-color selectable backlight with four brightness levels each. Colors are: Blue, Red, Green and White
- Compatible with many brands of tablets including Zebra, Xplore, Getac, Panasonic, Ruggon, Dell and more through USB connection
- Fully mountable
- Easy to clean and disinfect with hospital-grade methods
- English, French Canadian and UK language layouts readily available. For other languages, please contact us.

Features:

- Durable ABS/polycarbonate case
- Ultra-wide, resistive touchpad
- Built-in Windows multimedia controls: Mute, Volume Control and Sleep mode, compatible with Windows 7/8/10
- Built-in 50 mm and 75mm mounting patterns
- Designed to meet MIL-STD-810G and built to IP65 standards
- Full sealed and suited to medical settings and lab use.
- Ask us about mounting solutions for public safety vehicles, including the mount from Mobile Mounts Inc. for tablets and laptops. This keyboard is usable with many types of existing mounting equipment.
- IK-82-SA can be used in any work space and can be mounted in a vehicle, or part of a panel.

This solution is a mountable, stand alone keyboard and can be used with a variety of brands of tablets. No matter



which CPU or if you upgrade, you can use iKey's IK-82-SA keyboard.

Product Code IK-82-SA

Certifications	FCC/CE/IC & MIL-STD-810G
Cable	4.5 ft USB Cable
Key Switch	LIFE: 10 Million Cycles TRAVEL: 1.3mm Actuation Force: 65gf Feedback: Tactile Click
Vibration	0.04g/Hz @ 20-1000Hz, 1-hour/axis, 3 axes
Power	USB: 250mA@5V (from CPU port)
Compatibility	Windows, Mac Operating Systems
Temperature Range	STORAGE: -51C TO 71C (-60F TO 160F) OPERATING: -29C to +63C (-20F to 145F)
Weight	1.64 lb
Dimensions	12" x 8" x 0.875"
Warranty	Standard One Year Limited Warranty
Humidity	0-95%, Non-condensing
Model #	IK-82-SA