

# ZU2200

High brightness professional WUXGA laser projector

---



- **22,000 lumen WUXGA DLP laser projector**
- **Optional lenses allowing for installation flexibility**
- **Ultimate reliability with built in redundancy mode**
- **Pure engine video processing and color matching**

The ZU2200 offers enhanced features such as MultiColor Laser (MCL) technology. Part of the DuraCore laser line up, it combines longer-lifetime light source and an independent IP rated dust certification for ultimate peace of mind.

Delivering an astonishing 30,000 hours, this projector achieves superior color rendition through MultiColor laser technology producing visually striking lifelike images with exceptional detail.

Designed for even the most complex professional installations, the ZU2200 offers a selection of interchangeable lens options for ultimate flexibility.

Designed for high end installations with a multitude of connectivity options and failsafe redundancy mode.

## Specifications

The following specifications are preliminary and subject to change without notice

### Display/image

Display technology	DLP
Resolution	WUXGA (1920x1200)
Brightness	22,000 lumens
ANSI brightness	18,500 lumens
Contrast ratio	2,000,000:1
Native aspect ratio	16:10
Aspect ratio - compatible	16:9, 16:10
Screen size	Dependent on lens

### Lamp info

Light source type	DuraCore MultiColor Laser
LASER life	30,000 hours

### Optical

Throw ratio	Dependent on lens
Projection distance	Dependent on lens

### Connectivity

Connections	<b>Inputs</b> 1 x RS232, 1 x 3D sync, 1 x Wired remote, 1 x HDBaseT, 1 x DisplayPort, 2 x HDMI, 1 x VGA, 1 x DVI-D, 1 x 3G-SDI <b>Outputs</b> 1 x RS232, 1 x 3D sync, 1 x Wired remote, 1 x HDMI, 1 x 3G-SDI <b>Control</b> 1 x RJ45, 1 x USB-A service, 1 x 12V trigger
-------------	--

### General

3D	Full 3D
IP rating	IP5X
OSD / display languages	2 languages: English
24/7 operation	Yes
360° operation	Yes
Remote control	Backlit ProAV remote

### Networking

LAN - display	No
LAN - wireless networking	No
LAN	Yes

### Weight and dimensions

Dimensions (W x D x H)	25.6" x 28" x 9.8"
------------------------	--------------------

Net weight	117.5 lbs
------------	-----------

UPC	796435 44 554 6
-----	-----------------

