

## PATH TO THE FUTURE



### Selling Points

- 1000R Perfect Curved Screen - Perfectly fits the curvature of the human eye so that you can see the entire screen without any fatigue.
- Rapid Boost (165 + 1ms) - Experience smooth gaming with a blazing fast refresh rate and response time, that gives you the upperhand in fast moving games.
- Night Vision: See every detail clearly in the dark, helping you find and attack enemies before they notice.
- AMD FreeSync Premium Technology - Tear free, stutter free, fluid gaming.
- Anti-Flicker and Less Blue Light - game even longer and prevent eye strain and fatigue.
- Frameless design - Ultimate gameplay experience.
- 178° wide view angle.



Picture and logos: Pictures Monitor



1. Headset Hanger
2. Macro Key
3. 5-way joystick navigator
4. Power Button
5. Power Jack
6. 1x Display Port (1.4)
7. 1x HDMI w/ CEC (2.0b)
8. 1x HDMI (2.0b)
9. 1x USB 2.0 Type-C Port (DP Alternate Mode)
10. 1x Earphone out
11. 2x USB 2.0 Type A
12. 1x USB 2.0 Type B Upstream Port
13. Kensington Lock

## Specification

<b>Color</b>	ID1/Black-Black
<b>Screen Size</b>	27" (69 cm)
<b>Active Display Area (mm)</b>	596.736(H) x 335.664(V)
<b>Curvature</b>	Curve 1000R
<b>Panel Type</b>	VA
<b>Resolution</b>	1920x1080 (FHD)
<b>Aspect Ratio</b>	16:9
<b>Dynamic Refresh Rate technology</b>	FreeSync Premium
<b>HDR (High dynamic range)</b>	HDR ready
<b>SDR Brightness (nits)</b>	300
<b>HDR Brightness (Peak nits)</b>	NA
<b>Contrast Ratio</b>	3000:1
<b>DCR (Dynamic Contrast Ratio)</b>	100000000:1
<b>Signal Frequency</b>	104~186.8 KHz(H) / 48~165 Hz(V)
<b>Refresh Rate</b>	165Hz
<b>Response Time (MPRT)</b>	1ms(MPRT)
<b>Response Time (GTG)</b>	4ms
<b>Response Time (Tr + Tf)</b>	20ms
<b>View Angles</b>	178°(H)/178°(V)
<b>NTSC (CIE1976 area percentageoverlap)</b>	101.5%/84.27%
<b>NTSC (CIE1931 area percentageoverlap)</b>	84.2%/77.84%
<b>sRGB (CIE1976 area percentageoverlap)</b>	116.42%/99.51%
<b>sRGB (CIE1931 area percentageoverlap)</b>	118.87%/99.88%
<b>Adobe RGB (CIE1976 area percentageoverlap)</b>	99.76%/89.01%
<b>Adobe RGB (CIE1931 area percentageoverlap)</b>	88.1%/81.87%
<b>DCI-P3 (CIE1976 area percentageoverlap)</b>	92.72%/92.31%
<b>DCI-P3 (CIE1931 area percentageoverlap)</b>	87.63%/87.38%
<b>Rec.709 (CIE1976 area percentageoverlap)</b>	116.42%/99.51%
<b>Rec.709 (CIE1931 area percentageoverlap)</b>	118.87%/99.88%
<b>Surface Treatment</b>	Anti-glare
<b>Display Colors</b>	1.07B
<b>Color bit</b>	10 bits (8 bits + FRC)
<b>Note_DP</b>	1920 x 1080 (Up to 165Hz)
<b>Note_HDMI</b>	1920 x 1080 (Up to 165Hz)
<b>Note_DVI</b>	N/A
<b>Rec.2020 (CIE1976 area percentageoverlap)</b>	N/A
<b>Rec.2020 (CIE1931 area percentageoverlap)</b>	N/A
<b>HDMI</b>	2
<b>HDMI version</b>	2.0b
<b>HDMI HDCP version</b>	2.2
<b>DisplayPort</b>	1
<b>DisplayPort version</b>	1.2a
<b>DisplayPort HDCP version</b>	2.2
<b>Thunderbolt version</b>	NA
<b>Thunderbolt HDCP version</b>	NA
<b>USB Type C (DisplayPort Alternate)</b>	1
<b>DVI</b>	NA
<b>D-Sub</b>	NA
<b>Mic-in</b>	NA
<b>Mic-in upstream</b>	NA
<b>Headphone-out</b>	1
<b>Audio Combo</b>	NA
<b>USB 2.0 Type B</b>	1
<b>USB 3.2 Gen 1 Type B</b>	NA
<b>Lock type</b>	Kensington Lock
<b>Speaker</b>	N/A
<b>Power Type</b>	External Adaptor 20V 4.5A
<b>Power Input</b>	100~240V, 50/60Hz
<b>Adapter's KC safety Number</b>	SU10469-16001
<b>Power Cord Type</b>	C5
<b>QC Output</b>	NA
<b>QC Output Power</b>	NA
<b>PD Output</b>	NA



MONITOR

## MAG ARTYMIS 274CP

MAG ARTYMIS 274 CP

<b>PD Output Power</b>	15W
<b>Adjustment (Tilt)</b>	-5° ~ 20°
<b>Adjustment (Swivel)</b>	-30° ~ 30°
<b>Adjustment (Height)</b>	0 ~ 100 mm
<b>Adjustment (Pivot)</b>	NA
<b>VESA Mounting</b>	100x100mm
<b>Frameless Design</b>	Yes
<b>Outer Carton Dimension (WxDxH) (mm)</b>	790 x 238 x 515
<b>Outer Carton Dimension (WxDxH) (inch)</b>	31.1 x 9.37 x 20.28
<b>Product Dimension with Stand (WxDxH) (mm)</b>	607.08 x 260.88 x 527.81
<b>Product Dimension with Stand (WxDxH) (inch)</b>	23.9 x 10.27 x 20.78
<b>Product Dimension without Stand (WxDxH) (mm)</b>	607.08 x 122.64 x 372.21
<b>Product Dimension without Stand (WxDxH) (inch)</b>	23.9 x 4.83 x 14.65
<b>Thunderbolt</b>	NA
<b>USB 2.0 Type A</b>	2
<b>USB 2.0 Type C</b>	NA
<b>USB 3.2 Gen 1 Type A</b>	NA
<b>USB 3.2 Gen 1 Type C</b>	NA
<b>USB 3.2 Gen 2x2 Type C</b>	NA
<b>USB 3.2 Gen 2x2 Type A</b>	NA
<b>Card Reader</b>	NA
<b>Stand Dimension (WxDxH) (mm)</b>	633.4 x 317.9 x 393.25
<b>Stand Dimension (WxDxH) (inch)</b>	24.94 x 12.52 x 15.48
<b>WebCam</b>	N/A
<b>Weight Without Stand (kg)</b>	N/A
<b>Inside Carton Dimension (WxDxH) (mm)</b>	775 x 223 x 490
<b>Inside Carton Dimension (WxDxH) (inch)</b>	30.51 x 8.78 x 19.29
<b>Weight (Net kg)</b>	6
<b>Weight (Gross kg)</b>	9.2
<b>DisplayPort Cable</b>	1
<b>HDMI Cable</b>	1
<b>DVI Cable</b>	0
<b>USB Type A to Type B Cable</b>	1
<b>USB Type C to Type A Cable</b>	0
<b>USB Type C to Type C Cable</b>	0
<b>Thunderbolt Cable</b>	0
<b>VGA Cable</b>	0
<b>3.5mm audio Cable</b>	0
<b>3.5mm combo audio Cable</b>	0
<b>Mouse Bungee Unit</b>	N/A
<b>VESA Screw</b>	N/A
<b>Warranty</b>	24M
<b>Power Cord</b>	1
<b>AC Adaptor</b>	1
<b>Quick Guide</b>	1
<b>Warranty Card</b>	1
<b>EAN</b>	4719072819675