



SPECIFICATIONS

| | |
|--|--|
| Panel Size | 32" (81.29 cm) |
| Panel Resolution | 2560 x 1440 (WQHD) |
| Refresh Rate | 175HZ |
| Response time | 1ms GTG |
| DYNAMIC REFRESH RATE TECHNOLOGY | G-sync Compatible |
| ACTIVATED RANGE | 0 - 175 Hz |
| Panel Type | Rapid IPS |
| Brightness (nits) | 400 nits (Typ), 600nits (Peak) |
| Viewing Angle | 178° / 178° |
| Aspect Ratio | 16:9 |
| Contrast Ratio | 1000:1 |
| DCR | 100000000:1 |
| Pixel Pitch (H x V) | 0.27675(H) x 0.27675(V) |
| Surface Treatment | Anti-glare |
| Display Colors | 1.07B |
| DCI-P3 / sRGB | 95% / 144% |
| Video ports | 2x HDMI (Supports WQHD@144Hz as specified in HDMI 2.0b) 1x DP (Supports WQHD@175Hz as specified in DisplayPort 1.4a) 1x USB Type C (DP alt.) |
| USB ports | 3x USB3.2 Gen 1 Type A 1x USB3.2 Gen 1 Type B |
| Audio ports | 1x Mic-in 1x Headphone-out 1x Audio combo jack |
| Active Display Area (mm) | 708.48 (H) x 398.52(V) |
| Kensington Lock | Yes |
| VESA Mounting | 100 x 100 mm |
| Control | 5-way OSD navigation joystick |
| Power Input | 100~240V, 50/60Hz |
| Signal Frequency | 48 to 175Hz |
| Adjustment (Tilt) | -5~20 |
| Adjustment (Swivel) | -30~30 |
| Adjustment (Height) | 0~100mm |

FEATURES



| | |
|-------------------------------------|--|
| Console Mode | 2K Resolution PS5™ Optimization FHD @ 120Hz WQHD @ 120Hz * All trademarks and the registered trademarks are the property of their respective owners. |
| Power consumption | 42W |
| Compatibility | PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook *All trademarks and the registered trademarks are the property of their respective owners. |
| Carton Dimension (W X H X D) | 975 x 181 x 550 mm |
| Dimension (W x H x D) | 727 x 251 x 482 mm |
| Weight (NW / GW) | 10.2 / 13.9 kg |
| Frameless Design | Yes |
| Note | Display Port: 2560 x 1440 Up to 175Hz) Type C (DP alt.): 2560 x 1440 (Up to 175Hz) HDMI: 2560 x 1440 (Up to 144Hz) The color gamut follows the CIE 1976 testing standard. |
| PIP / PBP Function | Yes |

CONNECTIONS



1. 5-way Joystick Navigator
2. Power Button
3. DC Jack
4. 1x HDMI w/CEC (2.0)
5. 1x HDMI (2.0)
6. 1x Display Port (1.4)
7. 1x USB Type C
8. Earphone out
9. 2x USB2.0 Type A
10. 1x USB2.0 Type B
11. Macro Key
12. Kensington Lock