

OS	Windows 11 Home
Color	Black
Screen Size / Type	15.6" FHD, IPS-Level 144Hz 45%NTSC
Resolution/ Ratio	1920x1080 16:9
CPU/Processor	Core i7-11800H 8 Core
CPU Frequency	2.4 - 4.6GHz
Chipset	HM570
Graphics	NVIDIA GeForce® RTX3050 TI Laptop GPU
Video Memory	4G GDDR6
System Memory	DDR IV 8GB*2
SoDimm	2 Sockets; Max Memory 64GB
HDD Capacity	512GB NVMe PCIe SSD
HDD Interface	NVMe
SSD	1x M.2 SSD slot (NVMe PCIe Gen3) 1x 2.5" SATA HDD
LAN	Gb LAN
WLAN	Intel Wi-Fi 6 AX201(2*2 ax)
BT	BT 5.1
HDMI-out	4K @ 60Hz
USB Type C	USB 3.2 Gen1 Type C *1
USB	USB 3.2 Gen1 *3
Keyboard	Red keyboard with Anti-Ghost key (84 Key)
Touch Pad	Multi Touch
Mic-in/ Headphone-out	1x Mic-in 1x Headphone-out
Speaker	2W*2
Webcam	720p HD Webcam
Battery Pack	3 cell (51Whr) Li-Polymer
AC Adapter	120W
Unit weight	4.10 lbs
Unit Dimension	14.13"x9.99"x0.85"
UPC	824142272725
UCC-14	10824142272722
Warranty	1 year Limited warranty (Include 1 Year Global)