

## Key Features

- ULTRA-WIDE VIEWING ANGLES |
- FRAMELESS DESIGN | A MORE
- COMFORTABLE WORKSPACE |
- ENVIRONMENTALLY FRIENDLY PACKAGING
- | CONVENIENT & VERSATILE STAND




## Product Description

Designed for the modern day office, the ViewSonic® VG2448a monitor delivers an efficient end-to-end enterprise experience. Featuring SuperClear® IPS panel technology and 1080p resolution, this 24" (23.8" viewable) monitor delivers crisp and clear images from nearly any viewing angle. The 3-sided thin bezel design provides a seamless viewing experience for multi-monitor setups. For enhanced productivity, an advanced ergonomic design offers a wide range of customizable adjustments for maximum comfort including pivot, swivel, height adjustment, and tilt. With the ability to tilt an impressive 40-degrees, the VG2448a is ideal for users who prefer to work while standing up, as well as for those who like to use their screen for group discussions. Versatile connectivity options include HDMI, DisplayPort, VGA, and USB. This monitor is also shipped in eco-friendly biodegradable packaging, along with an easy-to-install quick release stand that makes for simple out-of-the box setup. The quick release stand also includes an integrated client mount and cable management features, making this monitor perfect for deployment in cloud-based environments.




- 01. Menu Control Panel
- 02. VESA Compatible Wall Mount (100 x 100 mm)
- 03. AC In
- 04. HDMI 1.4 In
- 05. DisplayPort In
- 06. USB Type-A (x2)
- 07. Kensington Lock Slot
- 08. Internal Speakers
- 09. USB Type-A (x2)
- 10. USB Type-B
- 11. VGA



24" DISPLAY



IPS PANEL



1920 x 1080 RESOLUTION

call: 888.881.8781

### Contact Sales

email: [salesinfo@viewsonic.com](mailto:salesinfo@viewsonic.com)

visit: [viewsonic.com](http://viewsonic.com)

#### Display:

Display Size (in.):	24
Viewable Area (in.):	23.8
Panel Type:	IPS
Resolution:	1920 x 1080
Resolution Type:	Full HD (1920x1080)
Static Contrast Ratio:	1,000:1
Dynamic Contrast Ratio:	50,000,000:1
Light Source:	LED
Brightness:	250 cd/m2
Colors:	16.7M
Color Space Support:	6 bit + A-FRC
Aspect Ratio:	16:9
Response Time (Typical GTG):	5ms
Viewing Angles:	178° horizontal, 178° vertical
Backlight Life (Hours):	30,000
Panel Surface:	Anti-Glare type, Hard-coating (3H), Haze 25%

#### Compatibility:

PC Resolution (max):	1920 x 1080
Mac® Resolution (max):	1920 x 1080

#### Connector:

USB Type A(4), USB Type B(1), VGA(1), HDMI 1.4 In(1), DisplayPort(1)

#### Audio:

Internal Speakers:	2W (x2)
--------------------	---------

#### Power:

Eco Mode (Conserve):	16.5W
Eco Mode (optimized):	17.5W
Consumption (typical):	19.5W
Consumption (max):	53.9W
Voltage:	AC 100-240V (universal), 50-60Hz
Stand-by:	0.5W
Power Supply:	Internal

#### Additional Hardware:

Kensington Lock Slot:	1
-----------------------	---

#### Controls:

Physical Controls:	Key 1 (eye), Key 2, Key 3, Key 4, Key 5, Key 6 (power)
On Screen Display:	Input Select, Audio Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu

#### Operating Conditions:

Temperature:	32-104° F (0 - 40° C)
Humidity (non-condensing):	20-90%

#### Mount:

VESA Compatible:	100 x 100 mm
------------------	--------------

#### Video Signal:

Frequency Horizontal:	VGA, HDMI(1.4), DisplayPort: 24 ~ 82KHz
Frequency Vertical:	VGA, HDMI(1.4), DisplayPort: 50 ~ 75 Hz

#### Ergonomics:

Height Adjust:	130 mm / 5.1 in
Swivel:	120°
Pivot (Right/Left):	90° / 90°
Tilt (Forward/Back):	5° / 40°

#### Weight (imperial):

Net (lbs):	13.6
Net Without Stand (lbs):	8.4
Gross (lbs):	19.8

#### Weight (metric):

Net (kg):	6.2
Net Without Stand (kg):	3.8
Gross (kg):	9.0