




Z30 POS Stand

For I-Series 4 Slate for Android



Integrated I/O



Concealed Cable Routing



Built-in CFD

Product Overview

The Z30 delivers a beautifully robust point-of-sale stand complete with a built-in customer-facing touchscreen display, integrated connectivity hub and concealed cable routing. Designed to support Elo's Android I-Series 4 Slate, the Z30 POS stand includes a universal VESA mount making it easy to install the 15.6-inch Full HD touchscreens with your choice of Qualcomm or Rockchip processor options.

Start changing the way customers and employees interact by deploying a new generation of interactive point-of-sale technologies that provide seamless integration, effortless provisioning and simplified device management via EloView or your preferred management tools.

Offer customers a point of interaction with an optional built in interactive CFD

Integrated connectivity hub built into the stand with a compartment for seamless cable routing

Compatible with the I-Series 4 Slate 15.6-inch Full HD interactive display

Z30 POS Stand

Specifications	
Color	Dark Grey Metallic
Compatibility	Main Display: I-Series 4 Slate Customer-Facing Displays (for use of non-CFD stand): 0702L - Elo P/N: E796382 1002L - Elo P/N: E155834 and E324341 1302L - Elo P/N: E683595 and E683787 1502L - Elo P/N: E125496
I/O Ports	DC Input 4 x USB-A 3.0 (900mA) RJ45 Ethernet LAN (Gigabit) RJ12 (Serial/cash drawer)* 12/24V Powered USB 24V USB-C output - CFD (DisplayPort, Touch and Power Delivery up to 27W) *User will need to select mode
Display Head Connection	USB Type C
Power	AC input voltage: 100-240 VAC Input frequency: 50-60 Hz
Power Consumption	On - Without CFD: 3.5W; With CFD: 8.32W Off: <0.1W Sleep - Without CFD: 2.5W; With CFD: 8.32W
Real-Time Clock	Lithium coin cell battery
Dimensions (W x D x H)	6.34" x 9.55" x 7.99" / 162 mm x 242.6 mm x 203 mm
Shipping Dimensions	11.65" x 11.42" x 12.6" / 296 mm x 290 mm x 320 mm
Weight	5.7 lbs / 2.6 kg
Shipping Weight	10.8 lbs / 4.9 kg
Temperature	Operating: 32°F to 104°F (0°C to 40°C) Storage: -4°F to 122°F (-20°C to 50°C)
Humidity	Operating: 20%-80% Storage: 5%-95%
Mounting Options	VESA 75mm
MTBF	50,000 hours
Warranty	2 years standard
Extended Warranty	3 year warranty coverage - Elo P/N: E375367 4 year warranty coverage - Elo P/N: E375573 5 year warranty coverage - Elo P/N: E375771 2 year warranty coverage + AUR - Elo P/N: E375970 3 year warranty coverage + AUR - Elo P/N: E376169 4 year warranty coverage + AUR - Elo P/N: E376362 5 year warranty coverage + AUR - Elo P/N: E376547
Regulatory Approvals	FCC (US) Class B (With CFD Model is Class A only); IC (Canada); CE (Europe); VCCI (Japan); RCM (Australia)
What's in the Box	Z30 POS Stand , North America Power Cable, European Power Cable, Quick Install Guide, 150W Power Brick, 2 x Zip Ties, 1 x M3 x6mm screws, 4 x M4x6 mm screws, 1 x M4x8 mm screw, Base Plate - for mounting to a countertop

Built-In Customer-Facing Display

Specifications	
Size Resolution	10.1 inch 1280x800 @ 60 Hz
Active Display Area	8.7" x 5.3" / 216.96 mm x 135.6 mm
Operating System	Horizontal: ±80° or 160° total / Vertical: ±80° or 160° total
Processor	LCD Panel: 400 nits; TouchPro PCAP: 344 nits
Number of Colors	8-bit (16.7M)
Touch Technology	TouchPro® PCAP (Projected Capacitive) - up to 10 touches
Sealing	Touchscreen sealed to LCD

Ordering Information

Part Number	Customer-Facing Display
E483135	Z30 POS Stand Without CFD
E482940	Z30 POS Stand With CFD

Learn more about Elo at [EloTouch.com](https://www.elotouch.com).

Americas

Tel +1 408 597 8000
elosales.na@elotouch.com

Europe (EMEA)

Tel +32 16 930 136
EMEA.Sales@elotouch.com

Asia Pacific

Tel +86 (21) 3329 1385
EloAsia@elotouch.com

Elo reserves the right to change or update, without notice, any information contained herein; to change, without notice, the design, construction, materials, processing or specifications of any products; and to discontinue or limit production or distribution of any products. Elo, the Elo logo and TouchPro are either trademarks or registered trademarks of Elo Touch Solutions, Inc. All other trademarks are the property of their respective owners. © 2022 Elo Touch Solutions, Inc. All rights reserved. 22061AES00163

