

# UHZ50

Smart 4K UHD laser home entertainment projector



- **True 4K UHD resolution and laser technology - HDR and HLG compatible**
- **Lights on viewing - 3000 lumens of brightness**
- **PureMotion reduces motion judder - 16.7ms input lag in 4K at 60Hz and 4ms in 1080P at 240Hz**
- **Android Launcher and Marketplace Apps - Four corner correction, 1.3x zoom and vertical lens shift**



Get ready for a whole new cinematic experience in the comfort of your own home. The stylish UHZ50 laser projector delivers vivid 4K UHD resolution for incredibly crisp images with exceptional clarity and vibrancy for movies, TV shows, games, and sports. With the included enhanced gaming mode, gamers can enjoy fast-moving action with a 16.7ms response time in 4K at 60Hz and 4ms in 1080P at 240Hz.

Packed with the latest technology and features, this stylish projector boasts HDR and HLG compatibility, three HDMI 2.0 inputs, seamless voice control, streaming apps and a built-in media player. Laser technology provides long-lasting, exceptional colour accuracy with extensive DCI-P3 coverage.

# Specifications

UPC: 796435 81 420 5, EAN: 5055387665828, Colour: White



## Display/image

Display technology	DLP™
Resolution	UHD (3840x2160)
Brightness	3,000 lumens
Contrast ratio	2,500,000:1
Native aspect ratio	16:9
Aspect ratio - compatible	4:3
Keystone correction - horizontal	+/-30°
Keystone correction - vertical	+/-30°
Has vertical auto keystone correction	Yes
Displayable colours (millions)	1073.4
Horizontal scan rate	15.375 ~ 91.146 KHz
Vertical scan rate	50 ~ 120HzHz
Uniformity	80%
Screen size	0.87m ~ 7.68m (34.1" ~ 302.4") diagonal

## Lamp info

Light source type	Laser
LASER life	30,000 hours

## Optical

Throw ratio	1.21:1 ~ 1.59:1
Projection distance (m)	1.2m - 8.1m
Zoom	1.3
Zoom type	Manual
Focal length (mm)	12.81mm~16.74mm
Lens shift	Vertical +10%
Native offset	105%
Lens shift	Yes - <a href="#">{{downloads_link}}</a>

## Connectivity

Connections	<b>Inputs</b> 2 x HDMI 2.0, 3 x USB-A, 1 x HDMI 2.0 (eARC) <b>Outputs</b> 1 x Audio 3.5mm, 1 x S/PDIF <b>Control</b> 1 x RS232, 1 x RJ45, 1 x 12V trigger, 1 x 3D sync
-------------	--

Wireless - technology	IEEE 802.11 a/b/g/n/ac
Wireless - security	WEP, TKIP, AES, WPA, WPA2
Wireless - antenna	Omnidirectional
Wireless - operating frequency	2.4GHz, 5GHz

## General

Noise level (typical)	27dB
Noise level (max)	29dB
PC compatibility	UHD, FHD, UXGA, SXGA, WXGA, HD, XGA, SVGA, VGA, Mac
2D compatibility	NTSC M/J, 3.58MHz, 4.43MHz PAL B/D/G/H/I/M/N, 4.43MHz SECAM B/D/G/K/K1/L, 4.25/4.4MHz 480i/p, 576i/p, 720p(50/60Hz), 1080i(50/60Hz), 1080p(50/60Hz)
3D compatibility	Side-by-Side:1080i50 / 60, 720p50 / 60 Frame-pack: 1080p24, 720p50 / 60 Over-Under: 1080p24, 720p50 / 60 Full 3D
3D	Full 3D
Security	Security bar, Kensington Lock, Password protected interface
OSD / display languages	11 languages: English, French, German, Italian, Portuguese, Russian, Chinese (simplified), Spanish, Chinese (traditional), Vietnamese
24/7 operation	Yes
Operating conditions	0°C~40°C/41°F~104°F, max altitude 3000M/9843ft, max humidity 85%
Remote control	Backlit home remote
Heat dissipation	785BTU/hour
Speaker count	2
Watts per speaker	10W
In the box	AC power cord Remote control inc CR2025 battery Quick start user manual USB wireless adapter

## Input lag

4.00ms

## Networking

Wireless - technology	IEEE 802.11 a/b/g/n/ac
Wireless - antenna	Omnidirectional
Wireless - operating frequency	2.4GHz, 5GHz

## Power

Power supply	100V ~ 240V, 50-60Hz
Power consumption (standby)	<0.5W
Power consumption (min)	175W
Power consumption (max)	230W

## Weight and dimensions

Dimensions (W x D x H) mm	337 x 265 x 119.3
Gross weight	6.5 kg
Net weight	4.8 kg

