



Planar PZN3210U

32" 4K Docking Monitor

The Planar® PZN3210U is a 32", 4K, USB Type-C Docking monitor. The integrated docking station provides a simple and easy way to connect a PC/laptop to the monitor. A single Type C cable provides audio, video, data, network connectivity via the gigabit Ethernet port, and power delivery up to 65 watts. The Planar PZN3210U is excellent for education, home, office or healthcare applications.



SPECIFICATION	DETAIL
Product Name	PZN3210U
Planar Part Number	998-2549-00
Viewable Size	31.5" diagonal (27.45" x 15.44")
Aspect Ratio	16:9
Contrast Ratio (typ)	1000:1
Viewing Angle (typ)	178° Horizontal and Vertical
Response Time (typ)	5 ms (GTG)
Brightness (Typical)	350 cd/m ²
Display Type	IPS LCD Active Matrix Flat Panel Display (TFT)
Display Resolution	3840 x 2160 UHD
Tilt Range	-6° to +24°
Palette	1.07 billion colors
Pixel Pitch	0.18159 mm
Refresh Rate	24-75Hz (60Hz recommended)
Dimensions (W x H x D)	31.7" x 24.1" x 14.7" (809.34 mm x 612.35 mm x 374.16 mm)

Dimensions without Stand	31.7" x 14.4" x 4.1" (809.34 mm x 365.83 mm x 104.6mm)
Panel Depth	4.1" (104.6 mm)
Display Weight	22.1 lb/10 kg (15.4 lb/ 7kg without stand)
Shipping weight	27.6 lb (12.5 kg)
Video Inputs	USB Type C (DisplayPort Alt Mode), DisplayPort, HDMI®
HDCP	Yes
Audio Output	Integrated 2W/channel stereo speakers, headphone jack
External Connections	USB Type C 24-pin, HDMI 19-pin, DisplayPort 20-pin, 3.5mm headphone out, USB 3.2 Gen 1 (Type A) x 3, RJ45.
USB	USB-C x 1 (Upstream) (5Gbps), USB3.2 Gen1 x 3 (Downstream)
USB C Power Delivery	USB C (Up to 65W) (5V/3A, 9V/3A, 12V/3A, 15V/3A, 20V/3.25A)
RJ45	Ethernet LAN (10M/100M/1000M)
Compatibility	PC and Mac® (adapter may be required for Mac)
Power Supply	Internal
Power Consumption (max)	35W typical (<0.5W standby)
Power Requirements	AC 100/240 VAC
Operating Temperature	0° to +40°C (32° to 104°F)
Humidity	20 - 90% RH (non-condensing)
Mount	Built-in 100 mm VESA, back
Product Approvals	cTUVus, CE , FCC-B, RoHS
Recommended Usage	Up to 16 hours per day
Service and Support	3-Year Customer First™ Warranty featuring FREE Advance Replacement (US only). Please see the warranty document for more details and for replacement procedures outside the US.
Options / Features	IPS panel, Wide color consistent viewing angle, Discreet branding, Height adjustment: 5.1" (130cmm), Swivel range 360° (180° left, 180° right), Pivot 90°, Anti-glare coating ,Multi-language display, On screen display (OSD), Kensington® Security Slot

Blue Light Reduction	Yes
Flicker Free	Yes
In the Box	PZN3210U 32" LCD Monitor, Power Cord, HDMI & DP Cable, USB Type-C Cable, User's Guide
UPC	8 10689 00924 5
HDMI®	Planar utilizes HDMI® standards in this product. The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI Trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

For more information, please visit www.planar.com

Specifications are subject to change without notice.

Specification Report Date: 11/18/2024

© Copyright 2024 Planar Systems, Inc. All rights reserved