

OS	Windows 11 Home
Color	Core Black
Screen Size / Type	15.6" FHD, IPS-Level 144Hz 45%NTSC
Resolution/ Ratio	1920x1080 16:9
CPU/Processor	Core i5-11400H 6 Core
CPU Frequency	2.7 - 4.5GHz
Chipset	HM570
Graphics	NVIDIA GeForce® RTX3060 Laptop GPU
Video Memory	6G GDDR6
System Memory	DDR IV 8GB*1
SoDimm	2 Sockets; Max Memory 64GB
HDD Capacity	512GB NVMe PCIe SSD
HDD Interface	NVMe
SSD	Up to 2 x NVMe PCIe Gen3 SSD
LAN	Gb LAN
WLAN	Intel Wi-Fi 6 AX201(2*2 ax)
BT	BT 5.1
HDMI-out	4K @ 60Hz
USB Type C	USB 3.2 Gen1 Type C *1
USB	USB 3.2 Gen1 *2 USB 2.0 *1
Keyboard	Red keyboard with Anti-Ghost key (99 Key)
Touch Pad	Multi Touch
Mic-in/ Headphone-out	1 Audio Combo (1/8")
Speaker	2W*2
Webcam	720p HD Webcam
Battery Pack	3 cell (53Whr) Li-Polymer
AC Adapter	180W
Unit weight	4.63 lbs
Unit Dimension	14.13"x10.20"x0.98"
UPC	824142274156
UCC-14	10824142274153
Warranty	1 year Limited warranty (Include 1 Year Global)