



Modern 15 A11MU-863CA

OS	Windows 11 Home (MSI recommends Windows 11 Pro for business.)
Color	Carbon Gray
Screen Size / Type	15.6" FHD, IPS-Level 60Hz 45%NTSCThin Bezel
Resolution/ Ratio	1920x1080 16:9
CPU/Processor	Core i5-1155G7
CPU Frequency	1.0 - 4.5GHz
Graphics	Intel Iris Xe
System Memroy	DDR IV 8GB*1
SoDimm	2 Sockets; Max Memory 64GB
HDD Capacity	256GB NVMe PCIe SSD
HDD Interface	NVMe
SSD	1x M.2 SSD NVMe PCIe Gen3x4, 1x M.2 SSD PCIe Gen4x4
WLAN	Intel Harrison Peak (2x2 802.11 ax)
BT	BT 5.2 (2x2)
Card Reader	Micro SD
HDMI-out	4K @ 30Hz
USB Type C	USB 3.2 Gen 2 Type C *1
USB	USB 3.2 Gen2 *2; 3.2 Gen1*1
Keyboard	White backlight 84 Key
Touch Pad	Multi Touch
Mic-in/ Headphone-out	Mic-in/Headphone-out Combo
Speaker	Speakers 2W * 2
Webcam	720p HD Webcam
Battery Pack	3 cell (52Whr) Li-Polymer
AC Adapter	65W
Unit weight	3.53 lbs
Unit Dimension	14.05" x 9.20" x 0.67"~0.71"
UPC	824142273807
UCC-14	10824142273804
Warranty	1 year Limited warranty (Include 1 Year Global)