

CMVR 324 / 325

Wisenet SKY Compact Cloud Managed Video Recorder



The Wisenet SKY Cloud Managed Video Recorder (CMVR) stores video and acts as a gateway from your premises to the Wisenet SKY Cloud Data Center where your video can also be stored and managed by the Wisenet SKY Cloud VMS. It provides secure video storage & video streaming, intelligent bandwidth management, and monitoring of cameras.

These small form factor CMVRs are designed for applications of up to 12 cameras when a server rack is not available. They are suitable for wall or shelf mounting. On-premises recording can be combined with cloud recording for additional redundancy, with an available subscription.

Key Features

- Supports up to 12 @ 1MP cameras ~ 8 @ 4MP cameras*
- Supports up to 5 cloud analytics, with supported license
- Intelligent Bandwidth Management with local recording up to 10 days (12 cameras @ 1MP)
- Dual gigabit network ports
- HDMI & DisplayPort video outputs for local display
- Compact form factor for wall or shelf mounting
- Fully cloud managed
- Supports motion or continuous recording
- Front panel indicator lights
- Supports Wisenet and ONVIF conformant IP cameras
- Complete encryption of video in transit and at rest

STANDARD SUPPORT (Included)

- Free of charge with an active subscription
- No cost replacement with an active subscription
- 24/7 email and web support
- Standard phone support

CMVR 324 / CMVR 325

SYSTEM	
Maximum Cameras @ 1MP	12 / 12
Maximum Cameras @ 4MP	8 / 8
Maximum Cloud Analytics	5
Hard Disk Drive	2TB / 2TB 2TB 10 days for 12 cameras @ 1MP
Network ports	Dual gigabit ethernet RJ-45 / Single gigabit ethernet
PoE Ports	0 / 4 PoE ports of IEEE802.3af class 3 (325 only)
Video output	1x HDMI, 1x DisplayPort
USB ports	2x USB 3.0
Operating System	Embedded Linux
Included accessories	Wall mount, power supply
Ordering SKU	EN-BR324-0 / EN-BR325-0


MECHANICAL / ELECTRICAL / ENVIRONMENTAL		
Mechanical	Form Factor	Compact wall or shelf mount
	Color / Material	324: Black / Plastic, 325 Black / Metal
	Dimensions	5.00" x 5.01" x 1.75" (125mm x 127mm x 47mm) 324 5.00" x 6.77" x 2.95" (127mm x 172mm x 75mm) 325
Electrical	Weight	1.4lb (0.64kg) 324 / 4.24lb (1.92kg) 325
	Power Supply	Included, 20 W / 22 W
	Power Input	100 ~ 240V AC
Environmental	Operating Temperature	32°F to 95°F (0°C to 35°C)
	Operating Humidity	0% to 70% RH, non-condensing
Certification	FCC, UL, PSE, CE, CCC(S&E), REACH, RoHS, C-Tick, NDA	

*The latest product information / specification can be found at www.hanwhasecurity.com

Please note:


An active subscription is required to use the Wisenet SKY Cloud VMS

***Typical - please utilize the Wisenet SKY VMS CMVR Wizard for precise capacity**



CMVR 324 / 325

Wisenet SKY Compact Cloud Managed Video Recorder



NETWORK FEATURES

- Automatic network configuration
- Secure camera network (dual network ports)
- No inbound connections needed
- Packet loss detection/reporting
- Network disconnected alerts

MANAGEMENT FEATURES

- Remote management
- Automatic camera discovery
- Automatic camera configuration
- Advanced motion detection
- Local video recording
- Configuration synced to Cloud
- Camera trouble alerts
- Internet outage alerts
- Fully cloud managed

MODEL	CMVR 324	CMVR 325
Maximum Cameras (1MP)*	12 IP	
Maximum Cameras (4MP)*	8 IP	
Maximum Analytic Count*	5	
Video Recording	10 days for 12 cameras @ 1MP	
Hard Drives	2TB spinning drive	
POE Camera Ports	None	4 IEEE802.3af Class 3
Network Ports	Dual Gigabit	Single Gigabit
Video Output	1x HDMI, 1x DisplayPort	
Dimension	125 x 127 x 50 mm 5.00 x 5.01 x 1.75 in	127 x 172 x 75 mm 5.00 x 6.77 x 2.95 in
Included power supply	External 100-240 VAC, 20 W	External 100-240 VAC, 22 W
Operating Temperature Range	0°C to 35°C 32°F to 95°F	-10°C to 50°C 14°F to 122°F
Operating Humidity Range	0 to 70%	
Certifications	FCC, UL, PSE, CE, CCC(S&E), REACH, RoHS, C-Tick, NDAA	

* Typical - please utilize the Wisenet SKY VMS CMVR Wizard for precise capacity