

H5T1M

2.7-13.5mm motorized lens, white housing



Features

- Supports up to 5MP TVI, 2MP AHD/CVI and CVBS by dip switch
- True WDR
- IR Range : ~65 ft (depending upon scene reflection)
- Motorized lens with auto focus
- Full OSD operation via UTC (up the coax)
- 12VDC operation (power supply not included)
- IP66 compliant, weather resistant
- 5 year warranty



Included Junction Box



Camera Specifications	
Image Sensor	1/2.8" CMOS
Maximum Resolution	5MP: 2592 x 1944
Field of View	30° ± 3° - 99° ± 2°
Filter	Removable IR Cut Filter
Video Output	TVI / CVI / AHD / CVBS
Minimum Illumination	0 lux (24PCs SMD led ON)
S/N Ratio	≥ 50dB
Image System	PAL: 50Hz/NTSC: 60Hz
White Balance	ATW (PRO default), Gray World Optional
True WDR	Default OFF (≥ 120dB)
3DNR	AUTO
AGC	ON
BLC	OFF
Defog	OFF/ON
Auto Exposure Mode	Yes

Operating & Unit Specifications	
Power	12VDC (power supply not included) (± 10%)
Operating Temperature	-22°F ~ 149°F
Storage Temperature	-22°F ~ 122°F
Unit Dimensions	4.72" (Dia) x 3.86" (H) (120mm x 98mm)
Unit Weight	1.74 lbs.

NDAA COMPLIANT

* Products are in compliance with NDAA Section 889 Part B Guidelines

Optional Accessory



PSW5
12VDC
Power Supply



TVIUTP
HD-TVI Balun
over UTP



TVIUTPPT
HD-TVI Balun over
UTP with Pigtail