

# Product data sheet

Specifications



APC Smart-UPS X, Line Interactive, 1000VA, Rack/tower convertible 2U, 120V, 8x 5-15R NEMA, SmartConnect port, Extended runtime, TAA

SMX1000CUS

## Overview

Lead time Usually in Stock

## Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	900 W
Rated power in VA	1000 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA 5-15P
output connection type	8 NEMA 5-15R
Provided equipment	CD with software
Range of Product	Smart-UPS

## Complementary

Communication Port SmartConnect Ethernet port  
SmartSlot

## Batteries & Runtime

Run Time	<a href="#">View Runtime Graph</a>
Efficiency	<a href="#">View Efficiency Graph</a>
Battery Charge Power (Watts)	99 W rated

## Physical

color Black

## Input

Efficiency at full load	75...154 V adjustable
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

## Output

Maximum configurable power in VA	1000 VA
Max Configurable Power (Watts)	900 W

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

Topology	Line Interactive
----------	------------------

---

Waveform Type	Sine wave
---------------	-----------

---

Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
----------------------------------	---------------------------------

## Conformance

---

Product Certifications	cUL Listed ENERGY STAR V2.0 (USA)
------------------------	--------------------------------------

## Environmental

---

Relative Humidity	0...95 %
-------------------	----------

---

Storage Relative Humidity	0...95 %
---------------------------	----------

## Ordering and shipping details

---

GTIN	731304424444
------	--------------

---

Country of origin	US
-------------------	----

## Packing Units

---

Unit Type of Package 1	PCE
------------------------	-----

---

Number of Units in Package 1	1
------------------------------	---

---

Package 1 Height	23.2 in (58.9 cm)
------------------	-------------------

---

Package 1 Width	24.4 in (62 cm)
-----------------	-----------------

---

Package 1 Length	9.7 in (24.6 cm)
------------------	------------------

---

Package 1 Weight	60.23 lb(US) (27.32 kg)
------------------	-------------------------

## Contractual warranty

---

Warranty	3 Years
----------	---------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

 Mercury Free

 RoHS Exemption Information Yes

## Environmental Certifications

 Energy Star® ENERGY STAR UPS V2.0 (USA)

## Certifications & Standards

**Reach Regulation** [REACH Declaration](#)

**Eu RoHS Directive** Compliant with Exemptions

**China RoHS Regulation** [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information.

**Environmental Disclosure** [Product Environmental Profile](#)

**Weee** The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

**Circularity Profile** [End of Life Information](#)