## Visioneer<sup>®</sup> Patriot<sup>™</sup> PH70 Scanner

# visioneer



Workgroup document capture leader adds secure network and mobile scanning.



Approved for official US Government use



EPEAT<sup>™</sup> Registered

et through daily document capture and archiving smarter and faster with the Visioneer® Patriot™ PH70 workgroup scanner. Built for paperheavy work environments, the Patriot™ PH70 duplex color scanner does the heavy lifting, digitizing forms and documents quickly and accurately. With scan speeds of up to 70 pages per minute and 140 impressions per minute, the Patriot™ PH70 has more horsepower (duty cycle of 11,000 daily scans) and handles more documents (up to 120 pages in the automatic document feeder) than any other scanner in its class. And, with the 25-point image processing engine of Visioneer Acuity software, customers get better quality scans the first time – and at full speed - adding even more productivity to the workday.

The Patriot<sup>™</sup> PH70 makes scanning and document management simple for both casual users and document capture professionals. Visioneer OneTouch<sup>®</sup> allows for one-click scanning presets and easy walk-up scanning capability with the push of a button, while Visioneer Capture SE makes batch scanning, editing, barcode reading and data extraction not only possible, but easy to implement. With Visioneer Organizer AI, automated classification of common files and tagging takes the time and frustration out of search. And, with a full-version ABBYY® FineReader® PDF, take intelligent archiving to the next level with searchable PDFs, comprehensive multilingual Optical Character Recognition (OCR), deep PDF editing, file conversions, and security.

Visioneer brings end-to-end workgroup connectivity to the Patriot<sup>™</sup> PH70, accommodating multiple users and delivering secure network and mobile scanning. With Visioneer Network Scan Service, Patriot<sup>™</sup> PH70 can be shared with network users, while the Visioneer Mobile Capture app makes document capture, editing and secure sharing on a smart phone or tablet a reality.

The Visioneer® Patriot™ PH70 delivers bestin-class value far beyond its price point and is backed by Visioneer's 3-year Standard Warranty. Combining performance, software and network/mobile scanning leadership, the Patriot™ PH70 is the solution for modern workgroup scanning.

## Visioneer<sup>®</sup> Patriot<sup>™</sup> PH70 Scanner

### VISIONEER INTELLIGENT SOFTWARE PLATFORM FOR WINDOWS

#### OneTouch

An easy-to-use scanner workflow application that performs all steps in a complex scanning operation at the touch of a button.

#### Acuity

Enables you to improve

scans. Acuity uses over

25 advanced algorithms

to intelligently correct

documents.

the visual clarity of

Capture SE

#### SE

Flexible, powerful batch scanning solution that can split scans into separate files, create indexes, read barcodes and extract data.

#### DriverPLUS

Provides an impressive array of settings to enable precise scan customization with a simple-to-use interface and helpful tool tips.

#### Organizer Al

Manages your files with fast search, conversion, file analysis and cleanup, tagging, PDF editor and automated file classification.

### ADDITIONAL SOFTWARE & DRIVERS

ABBYY" Software: ABBYY FineReader OCR Software Scanner Drivers for Windows: TWAIN™, ISIS, WIA

## SCANNER SPECIFICATIONS

Part Number	PH70-U
Scan Speed @ 200 dpi (ADF)	70 ppm / 140 ipm (Color, Grayscale, and B&W)
Scan Speed @ 300 dpi (ADF)	70 ppm / 140 ipm (Grayscale and B&W), 50 ppm / 100 ipm (Color)
Image Sensor	CIS
Light Source	LED
Optical Resolution	600 dpi
Output Bit Depth	24-bit Color / 8-bit Grayscale / 1-bit Black and White
Supported Scanning Resolutions	75, 100, 150, 200, 300, 400, 500, 600, 1200 dpi
Supported File Formats	BMP, PNG, GIF, JPEG, Single-Page PDF, Multi-Page PDF, TIFF, Multi-TIFF, RTF, TXT, XPS, DOC, DOCX, XLS, XLSX, PPT, PPTX
Background Color	Gray
ADF Capacity	120 Sheets (20 lb., 75-80 g/m <sup>2</sup> paper)
ADF Multi-Feed Detection	Ultrasonic Double Feed Detection
ADF Minimum Document Size	2" x 2" (50.8 x 50.8 mm)
ADF Maximum Document Size @ 200dpi	9.5" x 240" (241 mm x 6096 mm)
ADF Paper Thickness Range	7 - 110 lbs. (27 ~ 413 g/m²)
Card Scanning / Card Thickness	Yes (ADF) / 0.051" (1.25 mm)
Interface	USB 3.1 Gen1
Product Dimensions (W x H x D)	12.5" x 6.6" x 7.5" (316 x 168 x 191 mm) Paper Trays Collapsed
	12.5" x 9.4" x 26.8" (316 x 239 x 680 mm) Paper Trays Extended
Product Weight	10 lbs. (4.5 kg) Including Paper Trays
Daily Duty Cycle	11,000 Pages
Supported Operating Systems	Windows 11, 10, 7

Box Contents: Visioneer Patriot PH70 Scanner, Power supply and adapter, USB cable, Quick Install guide, Warranty and registration cards

For more information about Visioneer scanners visit www.visioneer.com

©2021 Visioneer Inc. All rights reserved. Visioneer®, Patriot<sup>TM</sup> and OneTouch® are trademarks of Visioneer. TWAIN is a trademark of TWAIN Working Group. All other trademarks are the property of their respective owners and are hereby acknowledged. Prices, features, applications, capabilities, appearance and availability of Visioneer products and services are subject to change without notice. 11/21

